


|        | millimetres | inches        |
|--------|-------------|---------------|
| L      | 1.6 ± 0.15  | 0.063 ± 0.006 |
| W      | 0.81 ± 0.15 | 0.032 ± 0.006 |
| T max. | 0.9         | 0.035         |
| t      | 0.35 ± 0.15 | 0.014 ± 0.006 |

## Basic Specifications


| Item                  | Unit | Spec.           | Conditions          |
|-----------------------|------|-----------------|---------------------|
| Capacitance           | nF   | 0.9 to 1.1      | @ 1 kHz, 1 Vrms     |
| DF                    | %    | 10 max.         | @ 1 kHz, 1 Vrms     |
| IR                    | GΩ   | 100 min.        | @ 50 Vdc, t = 120 s |
| DWV                   | Vdc  | 125             | @ I ≤ 50mA, t ≤ 5 s |
| Operating Temperature |      | -55°C to +125°C |                     |
| Dielectric            |      | X7R             |                     |
| AEC-Q200              |      | Not qualified   |                     |
| RoHS Compliant        |      | Yes             |                     |
| Termination           |      | Sn              |                     |

## Electrical Characteristics



(0603 50V X7R 1nF ±10%)

## Electrical Characteristics



# 06035C102KAT2A Datasheet

(0603 50V X7R 1nF ±10%)

## How To Order

| <u>0805</u>   | <u>5</u>   | <u>C</u>                     | <u>103</u>  | <u>M</u>  | <u>A</u>   | <u>T</u>   | <u>2</u>  | <u>A</u>                                   |
|---|--|------------------------------|---|---|--|--|---|--|
| <b>Size</b><br>(L" x W")  | <b>Voltage</b><br>4V = 4<br>6.3V = 6<br>10V = Z<br>16V = Y<br>25V = 3<br>50V = 5<br>100V = 1<br>200V = 2<br>500V = 7 | <b>Dielectric</b><br>X7R = C | <b>Capacitance Code</b> (In pF)<br>2 Sig. Digits +<br>Number of Zeros | <b>Capacitance Tolerance</b><br>J = ± 5%*<br>K = ±10%<br>M = ± 20%<br><br>*≤1µF only,<br>contact factory for<br>additional values | <b>Failure Rate</b><br>A = Not<br>Applicable<br>4=Automotive | <b>Terminations</b><br>T = Plated Ni and Sn<br>Z= FLEXITERM®**<br><br>*Optional termination<br><br>**See FLEXITERM®<br>X7R section | <b>Packaging</b><br>2 = 7" Reel<br>4 = 13" Reel<br><br><b>Contact<br/>Factory For<br/>Multiples</b> | <b>Special Code</b><br>A = Std.<br>Product |
| <p>NOTE: Contact factory for availability of Termination and Tolerance Options for Specific Part Numbers.<br/>Contact factory for non-specified capacitance values.</p>   |  |                              |   |   |  |  |   |  |
| <p><b>NOTICE:</b> Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.</p> |  |                              |   |   |  |  |   |  |