
KGM21BCG1C152JT Datasheet

(0805 16V C0G 1.5nF ±5%)

Dimensions




	millimetres (inches)
L	2.01 ± 0.20 (0.079 ± 0.008)
W	1.25 ± 0.20 (0.049 ± 0.008)
T max.	0.94 (0.037)
t	0.50 ± 0.25 (0.020 ± 0.010)

Basic Specifications


Item	*Unit*	*Spec.*	*Conditions*
Capacitance	nF	1.425 to 1.575	@ 1 kHz, 1 Vrms
DF	%	0.1 max.	@ 1 kHz, 1 Vrms
IR	GΩ	100	@ 16 Vdc,t =60 ± 5 s
DWV	Vdc	40	@ I ≤ 50mA, t ≤ 5 s
Op. Temperature	-55 °C to +125 °C		
Dielectric	C0G		
Product Level	General		
RoHS Compliant	Yes		
Termination	Sn		

Electrical Characteristics


|Z| & ESR [Ohm] vs Frequency [MHz]




S21 [dB] (50Ω, shunt) vs Freq. [MHz]




|Cap| [F] vs Frequency [MHz]




|ESL| [H] vs Frequency [MHz]



DF [%] vs Frequency [MHz]



Q [-] vs Frequency [MHz]




© KYOCERA AVX

KGM21BCG1C152JT Datasheet


(0805 16V C0G 1.5nF ±5%)

Electrical Characteristics


Typ. Cap. Change [%] vs Temperature [°C] Envelope



Cap.Change [%] vs Rated DC Voltage [%]



Phase Angle [°] vs Frequency [MHz]



Part Number Information

K	G	M	21		C	R5		1E		103	K		T	####
Symbol:	**Product Level:**	**Requirement:**	**Size:**		**Thickness:**	**Dielectric:**		**Voltage:**		**Capacitance:**	**Tolerance:**		**Packing:**	**Optional:**
KAVX	G General	M Standard	**Code:**	**EIA:**	See catalog	CG	C0G	**Multiplier:**	**Base:**	(2 significant digits	A ± 0.05 pF	H		See catalog for
	A Automotive	U Hi-Q (Special function)	02	01005	for list of	R5	X5R	0 1x	A 1	+ no of zeros)	B ± 0.1 pF	T		optional codes
	(AEC-Q200)	E ESD (Special function)	03	0201	codes	S6	X6S	1 10x	N 1.5		C ± 0.25 pF	U	Φ 180 (7 inch)*	
	M Medical	L Low inductance reverse Geometry	05	0402		T6	X6T	2 100x	D 2	**Examples:**	D ± 0.5 pF	Y		
		A Low Inductance LGA	15	0603		R7	X7R	3 1000x	E 2.5	100 = 10 pF	F ± 1 %	V		
		F Flexiterm (Special function/structure)	21	0805		S7	X7S		U 3	102 = 1000 pF	G ± 2 %			
		S Flexisafe (Special function/structure)	31	1206		T7	X7T		V 3.5	224 = 220 nF	J ± 5 %	M		
		G Gold Termination (Special Structure)	32	1210		R8	X8R		G 4	105 = 1 µF	K ± 10 %	L		
		C IDC (Special structure)	42	1808		L8	X8L		H 5		M ± 20 %	N	Φ 330 (13 inch)*	
		Q Ultra Low ESR	43	1812		G8	X8G		J 6.3			K		
			44	1825		V5	Y5V					S		
			55	2220				**Example:**						
			56	2225				1E = 25V (10 x 2.5)				X	Waffle pack	
			91	3640										

Note:
* See catalog for more information.

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are beleived to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.