
KGM21BCG1H471FT Datasheet

(0805 50V C0G 470pF ±1%)

Dimensions




	millimetres (inches)
L	2.01 ± 0.20 (0.079 ± 0.008)
W	1.25 ± 0.20 (0.049 ± 0.008)
T max.	0.94 (0.037)
t	0.50 ± 0.25 (0.020 ± 0.010)

Basic Specifications


Item	*Unit*	*Spec.*	*Conditions*
Capacitance	pF	465.3 to 474.7	@ 1 MHz, 1 Vrms
DF	%	0.1 max.	@ 1 MHz, 1 Vrms
IR	GΩ	100	@ 50 Vdc,t =60 ± 5 s
DWV	Vdc	125	@ I ≤ 50mA, t ≤ 5 s
Op. Temperature		-55 °C to +125 °C	
Dielectric		C0G	
Product Level		General	
RoHS Compliant		Yes	
Termination		Sn	

Electrical Characteristics


|Z| & ESR [Ohm] vs Frequency [MHz]




S21 [dB] (50Ω, shunt) vs Freq. [MHz]




|Cap| [F] vs Frequency [MHz]




|ESL| [H] vs Frequency [MHz]



DF [%] vs Frequency [MHz]



Q [-] vs Frequency [MHz]




© KYOCERA AVX

KGM21BCG1H471FT Datasheet


(0805 50V C0G 470pF ±1%)

Electrical Characteristics


Typ. Cap. Change [%] vs Temperature [°C] Envelope



Cap.Change [%] vs Rated DC Voltage [%]



Phase Angle [°] vs Frequency [MHz]



Part Number Information

K	G	M	21		C	R5		1E		103	K		T	####
Symbol:	**Product Level:**	**Requirement:**	**Size:**		**Thickness:**	**Dielectric:**		**Voltage:**		**Capacitance:**	**Tolerance:**		**Packing:**	**Optional:**
KAVX	G General	M Standard	**Code:**	**EIA:**	See catalog	CG C0G		**Multiplier:**	**Base:**	(2 significant digits	A ± 0.05 pF	H		See catalog for
	A Automotive	U Hi-Q (Special function)	02	01005	for list of	R5 X5R		0 1x	A 1	+ no of zeros)	B ± 0.1 pF	T		optional codes
	(AEC-Q200)	E ESD (Special function)	03	0201	codes	S6 X6S		1 10x	N 1.5		C ± 0.25 pF	U	Φ 180 (7 inch)*	
	M Medical	L Low inductance reverse Geometry	05	0402		T6 X6T		2 100x	D 2	**Examples:**	D ± 0.5 pF	Y		
		A Low Inductance LGA	15	0603		R7 X7R		3 1000x	E 2.5	100 = 10 pF	F ± 1 %	V		
		F Flexiterm (Special function/structure)	21	0805		S7 X7S			U 3	102 = 1000 pF	G ± 2 %			
		S Flexisafe (Special function/structure)	31	1206		T7 X7T			V 3.5	224 = 220 nF	J ± 5 %	M		
		G Gold Termination (Special Structure)	32	1210		R8 X8R			G 4	105 = 1 µF	K ± 10 %	L		
		C IDC (Special structure)	42	1808		L8 X8L			H 5		M ± 20 %	N	Φ 330 (13 inch)*	
		Q Ultra Low ESR	43	1812		G8 X8G			J 6.3			K		
			44	1825		V5 Y5V						S		
			55	2220				**Example:**						
			56	2225				1E = 25V (10 x 2.5)				X	Waffle pack	
			91	3640										

Note:
* See catalog for more information.

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are beleived to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.