
# KGM21NR71C103MT Datasheet

**(0805 16 V X7R 10nF ±20%)**

To download data and simulation models visit: SpiCAT ONLINE TOOL

KYOCERA AVX

## Dimensions






| | *millimetres* | *inches* |
|---|---|---|
| **L** | 2.01 ± 0.2 | 0.079 ± 0.008 |
| **W** | 1.25 ± 0.2 | 0.049 ± 0.008 |
| **T max.** | 1 | 0.039 |
| **t** | 0.5 ± 0.25 | 0.02 ± 0.01 |


## Basic Specifications


| *Item* | *Unit* | *Spec.* | *Conditions* |
|---|---|---|---|
| **Capacitance** | nF | 8 to 12 | @ 1 kHz, 1 Vrms |
| **DF** | % | 12.5 max. | @ 1 kHz, 1 Vrms |
| **IR** | GΩ | 100 min. | @ 16 Vdc, t = 120 s |
| **DWV** | Vdc | 40 | @ I ≤ 50mA, t ≤ 5 s |
| **Operating Temperature** | | -55°C to +125°C | |
| **Dielectric** | | X7R | |
| **Product Level** | | General | |
| **RoHS Compliant** | | Yes | |
| **Termination** | | Sn | |


## Electrical Characteristics







© KYOCERA AVX

# KGM21NR71C103MT Datasheet

**(0805 16 V X7R 10nF ±20%)**

## Electrical Characteristics





© KYOCERA AVX

# KGM21NR71C103MT Datasheet

## (0805 16 V X7R 10nF ±20%)

### Part Number Information

| K | G | M | 21 | C | R5 | 1E | 103 | K | T | #### |
|---|---|---|---|---|---|---|---|---|---|---|
| **Symbol:** | **Product Level:** | **Requirement:** | **Size:** | **Thickness:** | **Dielectric:** | **Voltage:** | **Capacitance:** | **Tolerance:** | **Packing:** | **Optional:** |
| KAVX | G General | M Standard | **Code:** **EIA:** | See catalog for list of codes | CG C0G | **Multiplier:** **Base:** | (2 significant digits + no of zeros) | A ± 0.05 pF | H | See catalog for optional codes |
| | A Automotive (AEC-Q200) | U Hi-Q (Special function) | 02 01005 | | R5 X5R | 0 1x A 1 | | B ± 0.1 pF | T | |
| | | E ESD (Special function) | 03 0201 | | S6 X6S | 1 10x N 1.5 | | C ± 0.25 pF | U | Φ 180 (7 inch)* |
| | M Medical | L Low inductance reverse Geometry | 05 0402 | | T6 X6T | 2 100x D 2 | **Examples:** | D ± 0.5 pF | Y | |
| | | A Low Inductance LGA | 15 0603 | | R7 X7R | 3 1000x E 2.5 | 100 = 10 pF | F ± 1 % | V | |
| | | F Flexiterm (Special function/structure) | 21 0805 | | S7 X7S | U 3 | 102 = 1000 pF | G ± 2 % | | |
| | | S Flexisafe (Special function/structure) | 31 1206 | | T7 X7T | V 3.5 | 224 = 220 nF | J ± 5 % | M | |
| | | G Gold Termination (Special Structure) | 32 1210 | | R8 X8R | G 4 | 105 = 1 µF | K ± 10 % | L | |
| | | C IDC (Special structure) | 42 1808 | | L8 X8L | H 5 | | M ± 20 % | N | Φ 330 (13 inch)* |
| | | Q Ultra Low ESR | 43 1812 | | G8 X8G | J 6.3 | | | K | |
| | | | 44 1825 | | V5 Y5V | | | | S | |
| | | | 55 2220 | | | **Example:** | | | | |
| | | | 56 2225 | | | 1E = 25V (10 x 2.5) | | | X | Waffle pack |
| | | | 91 3640 | | | | | | | |

**Note:**
* See catalog for more information.

**NOTICE:** Specifications are subject to change without notice. All statements, information and data given herein are beleived to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.