


Dimensions




| | millimetres | inches |
|--------|-----------------|-------------------|
| L | 1 ± 0.1 | 0.039 ± 0.004 |
| W | 0.5 ± 0.1 | 0.02 ± 0.004 |
| T max. | 0.56 | 0.022 |
| t | 0.25 ± 0.15 | 0.01 ± 0.006 |


Basic Specifications

| Item | Unit | Spec. | Conditions |
|-----------------------|------------|-----------------|-------------------------------|
| Capacitance | nF | 3.135 to 3.465 | @ 1 kHz, 1 Vrms |
| DF | % | 12.5 max. | @ 1 kHz, 1 Vrms |
| IR | G Ω | 100 min. | @ 16 Vdc, t = 120 s |
| DWV | Vdc | 40 | @ I \leq 50mA, t \leq 5 s |
| Operating Temperature | | -55°C to +125°C | |
| Dielectric | | X7R | |
| AEC-Q200 | | Not qualified | |
| RoHS Compliant | | Yes | |
| Termination | | FLEXITERM® | |

Electrical Characteristics



Electrical Characteristics



0402YC332JAZ2A Datasheet



(0402 16V X7R 3.3nF ±5% FLEXITERM®)

How To Order

| 0805 | 5 | C | 103 | M | A | T | 2 | A |
|--|---|-----------------------|---|---|--|---|---|--|
| Size (L" x W") | Voltage 4V = 4 6.3V = 6 10V = Z 16V = Y 25V = 3 50V = 5 100V = 1 200V = 2 500V = 7 | Dielectric X7R = C | Capacitance Code (In pF) 2 Sig. Digits + Number of Zeros | Capacitance Tolerance J = ± 5%* K = ±10% M = ± 20% *≤1µF only, contact factory for additional values | Failure Rate A = Not Applicable 4=Automotive | Terminations T = Plated Ni and Sn Z= FLEXITERM®** *Optional termination **See FLEXITERM® X7R section | Packaging 2 = 7" Reel 4 = 13" Reel Contact Factory For Multiples | Special Code A = Std. Product |
| NOTE: Contact factory for availability of Termination and Tolerance Options for Specific Part Numbers. Contact factory for non-specified capacitance values. | | | | | | | | |
| NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are beleived to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications. | | | | | | | | |