


06036C154MAT2A Datasheet

(0603 6.3V X7R 150nF ±20%)

To download data and simulation models visit: **SpiCAT** ONLINE TOOL




	millimetres	inches
L	1.6 ± 0.15	0.063 ± 0.006
W	0.81 ± 0.15	0.032 ± 0.006
T max.	0.9	0.035
t	0.35 ± 0.15	0.014 ± 0.006


Basic Specifications

Item	Unit	Spec.	Conditions
Capacitance	nF	120 to 180	@ 1 kHz, 1 Vrms
DF	%	12.5 max.	@ 1 kHz, 1 Vrms
IR	GΩ	6.6 min.	@ 6.3 Vdc, t = 120 s
DWV	Vdc	15.75	@ I ≤ 50mA, t ≤ 5 s
Operating Temperature		-55°C to +125°C	
Dielectric		X7R	
AEC-Q200		Not qualified	
RoHS Compliant		Yes	
Termination		Sn	

Electrical Characteristics



Electrical Characteristics



06036C154MAT2A Datasheet



(0603 6.3V X7R 150nF ±20%)

How To Order

<div>0805</div> <div>Size (L" x W")</div>	<div>5</div> <div>Voltage</div> <div>4V = 4</div> <div>6.3V = 6</div> <div>10V = Z</div> <div>16V = Y</div> <div>25V = 3</div> <div>50V = 5</div> <div>100V = 1</div> <div>200V = 2</div> <div>500V = 7</div>	<div>C</div> <div>Dielectric</div> <div>X7R = C</div>	<div>103</div> <div>Capacitance Code (In pF)</div> <div>2 Sig. Digits + Number of Zeros</div>	<div>M</div> <div>Capacitance Tolerance</div> <div>J = ± 5%*</div> <div>K = ±10%</div> <div>M = ± 20%</div> <div> </div> <div>*≤1µF only, contact factory for additional values</div>	<div>A</div> <div>Failure Rate</div> <div>A = Not Applicable</div> <div>4=Automotive</div>	<div>T</div> <div>Terminations</div> <div>T = Plated Ni and Sn</div> <div>Z= FLEXITERM®**</div> <div> </div> <div>*Optional termination</div> <div> </div> <div>**See FLEXITERM® X7R section</div>	<div>2</div> <div>Packaging</div> <div>2 = 7" Reel</div> <div>4 = 13" Reel</div> <div> </div> <div>Contact Factory For Multiples</div>	<div>A</div> <div>Special Code</div> <div>A = Std. Product</div>
<div>NOTE: Contact factory for availability of Termination and Tolerance Options for Specific Part Numbers. Contact factory for non-specified capacitance values.</div>								
<div>NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are beleived to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.</div>								