

KGM15BR71H104KT Datasheet

(0603 50 V X7R 100nF ±10%)

To download data and simulation models visit: **SpiCAT** ONLINE TOOL



Dimensions




| | millimetres | inches |
|--------|-------------|---------------|
| L | 1.6 ± 0.15 | 0.063 ± 0.006 |
| W | 0.81 ± 0.15 | 0.032 ± 0.006 |
| T max. | 0.95 | 0.037 |
| t | 0.35 ± 0.15 | 0.014 ± 0.006 |


Basic Specifications

| Item | Unit | Spec. | Conditions |
|-----------------------|------|-----------------|---------------------|
| Capacitance | nF | 90 to 110 | @ 1 kHz, 1 Vrms |
| DF | % | 10 max. | @ 1 kHz, 1 Vrms |
| IR | GΩ | 10 min. | @ 50 Vdc, t = 120 s |
| DWV | Vdc | 125 | @ I ≤ 50mA, t ≤ 5 s |
| Operating Temperature | | -55°C to +125°C | |
| Dielectric | | X7R | |
| Product Level | | General | |
| RoHS Compliant | | Yes | |
| Termination | | Sn | |

Electrical Characteristics



Electrical Characteristics



KGM15BR71H104KT Datasheet



(0603 50 V X7R 100nF ±10%)

Part Number Information

| K | G | M | 21 | C | R5 | 1E | 103 | K | T | ### |
|-------------------------|---|--|------------|-------------------|-------------|---------------------|--------------------------------------|-------------|----------|--------------------------------|
| Symbol: | Product Level: | Requirement: | Size: | Thickness: | Dielectric: | Voltage: | Capacitance: | Tolerance: | Packing: | Optional: |
| KAVX | G General | M Standard | Code: EIA: | See catalog | CG C0G | Multiplier: Base: | (2 significant digits + no of zeros) | A ± 0.05 pF | H | See catalog for optional codes |
| A Automotive (AEC-Q200) | U Hi-Q (Special function) | E ESD (Special function) | 02 01005 | for list of codes | R5 X5R | 0 1x A 1 | | B ± 0.1 pF | T | |
| M Medical | L Low Inductance reverse Geometry | A Low Inductance LGA | 03 0201 | | S6 X6S | 1 10x N 1.5 | | C ± 0.25 pF | U | |
| | F Flexitem (Special function/structure) | S Flexisafe (Special function/structure) | 05 0402 | | T6 X6T | 2 100x D 2 | Examples: | D ± 0.5 pF | Y | |
| | G Gold Termination (Special Structure) | C IDC (Special structure) | 15 0603 | | R7 X7R | 3 1000x E 2.5 | 100 = 10 pF | F ± 1 % | V | |
| | Q Ultra Low ESR | | 21 0805 | | S7 X7S | U 3 | 102 = 1000 pF | G ± 2 % | | |
| | | | 31 1206 | | T7 X7T | V 3.5 | 224 = 220 nF | J ± 5 % | M | |
| | | | 32 1210 | | R8 X8R | G 4 | 105 = 1 μF | K ± 10 % | L | |
| | | | 42 1808 | | L8 X8L | H 5 | | M ± 20 % | N | |
| | | | 43 1812 | | G8 X8G | J 6.3 | | | K | |
| | | | 44 1825 | | V5 Y5V | | | | S | |
| | | | 55 2220 | | | Example: | | | | |
| | | | 56 2225 | | | 1E = 25V (10 x 2.5) | | | X | Waffle pack |
| | | | 91 3640 | | | | | | | |

Note:
* See catalog for more information.

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.