

# VC060303A100DP

(0603, 3.3Vdc, 0.1J, 30A, 1450pF, Sn Term)

Multilayer Chip Varistor Datasheet

## BASIC SPECIFICATION


Case Size [EIA]	0603
Operating Temperature	-55 to +125°C
Grade	General
Termination	Sn
RoHS	Yes
MSL Level	1
Packaging	T&R 7in (180mm)
Packaging Qty	1000 pcs



## ELECTRICAL CHARACTERISTICS

DC Working Voltage	3.3 Vdc
AC Working Voltage	2.3 Vac
Breakdown Voltage [1mA DC]	5.0±20% V
Clamping Voltage [8x20µs]	12V @ 1A
Max Leakage Current [Vdc, 25°C]	100 µA
Transient Energy [10x1000µs]	0.1 J
Peak Power [10x1000µs]	75 W
Peak Current Rating [8x20µs]	30 A
Typical Capacitance [1kHz, 0.5Vrms, 25°C]	1450 pF
Capacitance Tolerance	+100/-50%

## DIMENSIONS



	mm	inches
L	1.60±0.15	0.063±0.006
W	0.80±0.15	0.031±0.006
T	0.9 max	0.035 max
t	0.35±0.15	0.014±0.006

## SOLDERING PAD




	mm	inches
A	0.89	0.035
B	0.76	0.03
C	2.54	0.1
D	0.76	0.03

## HOW TO ORDER


<b>VC</b>	<b>0603</b>	<b>03</b>	<b>A</b>	<b>100</b>	<b>D</b>	<b>P</b>
Varistor Chip	Case Size	Working Voltage	Energy Rating	Clamping Voltage	Packaging	Termination
		03 = 3.3Vdc	A = 0.1J	100 = 12V	D = 7" reel (1,000pcs) R = 7" reel (4,000pcs) T = 13" reel (10,000pcs)	P = Sn

## TYPICAL CHARACTERISTICS


Temperature Derating (Energy, Current, Power)



Power Derating



Voltage / Current



S21

