

# KGM15BR71C334KT Datasheet

(0603 16 V X7R 330nF ±10%)

To download data and simulation models visit: **SpiCAT** ONLINE TOOL

**KYOCERA** AVX

## Dimensions









|        | millimetres | inches        |
|--------|-------------|---------------|
| L      | 1.6 ± 0.15  | 0.063 ± 0.006 |
| W      | 0.81 ± 0.15 | 0.032 ± 0.006 |
| T max. | 0.95        | 0.037         |
| t      | 0.35 ± 0.15 | 0.014 ± 0.006 |


## Basic Specifications

| Item                  | Unit | Spec.           | Conditions          |
|-----------------------|------|-----------------|---------------------|
| Capacitance           | nF   | 297 to 363      | @ 1 kHz, 1 Vrms     |
| DF                    | %    | 12.5 max.       | @ 1 kHz, 1 Vrms     |
| IR                    | GΩ   | 3 min.          | @ 16 Vdc, t = 120 s |
| DWV                   | Vdc  | 40              | @ I ≤ 50mA, t ≤ 5 s |
| Operating Temperature |      | -55°C to +125°C |                     |
| Dielectric            |      | X7R             |                     |
| Product Level         |      | General         |                     |
| RoHS Compliant        |      | Yes             |                     |
| Termination           |      | Sn              |                     |

## Electrical Characteristics



## Electrical Characteristics



# KGM15BR71C334KT Datasheet



(0603 16 V X7R 330nF ±10%)

## Part Number Information

| K       | G                       | M  | 21         | C                 | R5          | 1E                              | 103   | K   | T  | ###                            |
|---------|-------------------------|--|------------|-------------------|-------------|---------------------------------|---|---|--|--------------------------------|
| Symbol: | Product Level:          | Requirement:                             | Size:      | Thickness:        | Dielectric: | Voltage:                        | Capacitance:  | Tolerance:  | Packing:                                       | Optional:                      |
| KAVX    | G General               | M Standard                               | Code: EIA: | See catalog       | CG C0G      | Multiplier: Base:               | (2 significant digits + no of zeros)                                    | A ± 0.05 pF<br>B ± 0.1 pF<br>C ± 0.25 pF<br>D ± 0.5 pF<br>F ± 1 %<br>G ± 2 %<br>J ± 5 %<br>K ± 10 %<br>M ± 20 % | H<br>T<br>U<br>Y<br>V<br>M<br>L<br>N<br>K<br>S | See catalog for optional codes |
|         | A Automotive (AEC-Q200) | U Hi-Q (Special function)                | 02 01005   | for list of codes | R5 X5R      | 0 1x A 1                        |   |   |  |                                |
|         | M Medical               | E ESD (Special function)                 | 03 0201    |                   | S6 X6S      | 1 10x N 1.5                     |   |   |  |                                |
|         |                         | L Low Inductance reverse Geometry        | 05 0402    |                   | T6 X6T      | 2 100x D 2                      | Examples:<br>100 = 10 pF<br>102 = 1000 pF<br>224 = 220 nF<br>105 = 1 µF |   |  |                                |
|         |                         | A Low Inductance LGA                     | 15 0603    |                   | R7 X7R      | 3 1000x E 2.5                   |   |   |  |                                |
|         |                         | F Flexitem (Special function/structure)  | 21 0805    |                   | S7 X7S      | U 3                             |   |   |  |                                |
|         |                         | S Flexisafe (Special function/structure) | 31 1206    |                   | T7 X7T      | V 3.5                           |   |   |  |                                |
|         |                         | G Gold Termination (Special Structure)   | 32 1210    |                   | R8 X8R      | G 4                             |   |   |  |                                |
|         |                         | C IDC (Special structure)                | 42 1808    |                   | L8 X8L      | H 5                             |   |   |  |                                |
|         |                         | Q Ultra Low ESR                          | 43 1812    |                   | G8 X8G      | J 6.3                           |   |   |  |                                |
|         |                         |  | 44 1825    |                   | V5 Y5V      |                                 |   |   |  |                                |
|         |                         |  | 55 2220    |                   |             |                                 |   |   |  |                                |
|         |                         |  | 56 2225    |                   |             |                                 |   |   |  |                                |
|         |                         |  | 91 3640    |                   |             |                                 |   |   |  |                                |
|         |                         |  |            |                   |             | Example:<br>1E = 25V (10 x 2.5) |   |   |  |                                |
|         |                         |  |            |                   |             |                                 |   |   | X Waffle pack                                  |                                |

### Note:

\* See catalog for more information.

**NOTICE:** Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.