

# KGM21NR71C124JT Datasheet

(0805 16 V X7R 120nF ±5%)

To download data and simulation models visit: **SpiCAT** ONLINE TOOL



## Dimensions




	millimetres	inches
L	2.01 ± 0.2	0.079 ± 0.008
W	1.25 ± 0.2	0.049 ± 0.008
T max.	1	0.039
t	0.5 ± 0.25	0.02 ± 0.01


## Basic Specifications

Item	Unit	Spec.	Conditions
Capacitance	nF	114 to 126	@ 1 kHz, 1 Vrms
DF	%	12.5 max.	@ 1 kHz, 1 Vrms
IR	GΩ	8.3 min.	@ 16 Vdc, t = 120 s
DWV	Vdc	40	@ I ≤ 50mA, t ≤ 5 s
Operating Temperature		-55°C to +125°C	
Dielectric		X7R	
Product Level		General	
RoHS Compliant		Yes	
Termination		Sn	

## Electrical Characteristics



## Electrical Characteristics



# KGM21NR71C124JT Datasheet



(0805 16 V X7R 120nF ±5%)

## Part Number Information

K	G	M	21	C	R5	1E	103	K	T	###
Symbol:	Product Level:	Requirement:	Size:	Thickness:	Dielectric:	Voltage:	Capacitance:	Tolerance:	Packing:	Optional:
KAVX	G General	M Standard	Code: EIA:	See catalog	CG C0G	Multiplier: Base:	(2 significant digits + no of zeros)	A ± 0.05 pF B ± 0.1 pF C ± 0.25 pF D ± 0.5 pF F ± 1 % G ± 2 % J ± 5 % K ± 10 % M ± 20 %	H T U Y V M L N K S	See catalog for optional codes
	A Automotive (AEC-Q200)	U Hi-Q (Special function)	02 01005	for list of codes	R5 X5R	0 1x A 1				
	M Medical	E ESD (Special function)	03 0201		S6 X6S	1 10x N 1.5				
		L Low Inductance reverse Geometry	05 0402		T6 X6T	2 100x D 2	Examples:			
		A Low Inductance LGA	15 0603		R7 X7R	3 1000x E 2.5	100 = 10 pF			
		F Flexitem (Special function/structure)	21 0805		S7 X7S	U 3	102 = 1000 pF			
		S Flexisafe (Special function/structure)	31 1206		T7 X7T	V 3.5	224 = 220 nF			
		G Gold Termination (Special Structure)	32 1210		R8 X8R	G 4	105 = 1 µF			
		C IDC (Special structure)	42 1808		L8 X8L	H 5				
		Q Ultra Low ESR	43 1812		G8 X8G	J 6.3				
			44 1825		V5 Y5V					
			55 2220				Example:			
			56 2225				1E = 25V (10 x 2.5)			
			91 3640						X	Waffle pack

**Note:**  
\* See catalog for more information.

**NOTICE:** Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.