

VC120626D580TP

(1206, 26Vdc, 0.4J, 120A, 500pF, Sn Term)

Multilayer Chip Varistor Datasheet

BASIC SPECIFICATION


Case Size [EIA]	1206
Operating Temperature	-55 to +125°C
Grade	General
Termination	Sn
RoHS	Yes
MSL Level	1
Packaging	T&R 13in (330mm)
Packaging Qty	10000 pcs



ELECTRICAL CHARACTERISTICS

DC Working Voltage	26 Vdc
AC Working Voltage	18 Vac
Breakdown Voltage [1mA DC]	34.5±10% V
Clamping Voltage [8x20µs]	60V @ 1A
Max Leakage Current [Vdc, 25°C]	10 µA
Transient Energy [10x1000µs]	0.4 J
Peak Power [10x1000µs]	300 W
Peak Current Rating [8x20µs]	120 A
Typical Capacitance [1kHz, 0.5Vrms, 25°C]	500 pF
Capacitance Tolerance	+100/-50%

DIMENSIONS



	mm	inches
L	3.20±0.20	0.126±0.008
W	1.60±0.20	0.063±0.008
T	1.02 max	0.040 max
t	0.94 max	0.037 max

SOLDERING PAD




	mm	inches
A	1.02	0.04
B	2.03	0.08
C	4.06	0.16
D	1.65	0.065

HOW TO ORDER


VC	1206	26	D	580	T	P
Varistor Chip	Case Size	Working Voltage	Energy Rating	Clamping Voltage	Packaging	Termination
		26 = 26Vdc	D = 0.4J	580 = 60V	D = 7" reel (1,000pcs) R = 7" reel (4,000pcs) T = 13" reel (10,000pcs)	P = Sn

TYPICAL CHARACTERISTICS


Temperature Derating (Energy, Current, Power)



Power Derating



Voltage / Current



S21

