

VC120642L800DP

(1206, 42Vdc, 0.8J, 180A, 600pF, Sn Term)

Multilayer Chip Varistor Datasheet

BASIC SPECIFICATION


Case Size [EIA]	1206
Operating Temperature	-55 to +125°C
Grade	General
Termination	Sn
RoHS	Yes
MSL Level	1
Packaging	T&R 7in (180mm)
Packaging Qty	2000 pcs



ELECTRICAL CHARACTERISTICS


DC Working Voltage	42 Vdc
AC Working Voltage	32 Vac
Breakdown Voltage [1mA DC]	51.0±10% V
Clamping Voltage [8x20µs]	80V @ 1A
Max Leakage Current [Vdc, 25°C]	15 µA
Transient Energy [10x1000µs]	0.8 J
Peak Power [10x1000µs]	600 W
Peak Current Rating [8x20µs]	180 A
Typical Capacitance [1kHz, 0.5Vrms, 25°C]	600 pF
Capacitance Tolerance	+100/-50%

DIMENSIONS



	mm	inches
L	3.20±0.20	0.126±0.008
W	1.60±0.20	0.063±0.008
T	1.8 max	0.071 max
t	0.94 max	0.037 max

SOLDERING PAD



	mm	inches
A	1.02	0.04
B	2.03	0.08
C	4.06	0.16
D	1.65	0.065

HOW TO ORDER

VC	1206	42	L	800	D	P
Varistor Chip	Case Size	Working Voltage	Energy Rating	Clamping Voltage	Packaging	Termination
		42 = 42Vdc	L = 0.8J	800 = 80V	D = 7" reel (1,000pcs) R = 7" reel (2,000pcs) T = 13" reel (10,000pcs)	P = Sn


VC120642L800DP

(1206, 42Vdc, 0.8J, 180A, 600pF, Sn Term)


Multilayer Chip Varistor Datasheet

TYPICAL CHARACTERISTICS


Temperature Derating (Energy, Current, Power)



Power Derating



Voltage / Current



S21

