

VC120656F111TP

(1206, 56Vdc, 0.7J, 100A, 180pF, Sn Term)

Multilayer Chip Varistor Datasheet

BASIC SPECIFICATION


Case Size [EIA]	1206
Operating Temperature	-55 to +125°C
Grade	General
Termination	Sn
RoHS	Yes
MSL Level	1
Packaging	T&R 13in (330mm)
Packaging Qty	2000 pcs



ELECTRICAL CHARACTERISTICS

DC Working Voltage	56 Vdc
AC Working Voltage	40 Vac
Breakdown Voltage [1mA DC]	68.0±10% V
Clamping Voltage [8x20µs]	110V @ 1A
Max Leakage Current [Vdc, 25°C]	15 µA
Transient Energy [10x1000µs]	0.7 J
Peak Power [10x1000µs]	525 W
Peak Current Rating [8x20µs]	100 A
Typical Capacitance [1kHz, 0.5Vrms, 25°C]	180 pF
Capacitance Tolerance	+100/-50%

DIMENSIONS



	mm	inches
L	3.20±0.20	0.126±0.008
W	1.60±0.20	0.063±0.008
T	1.7 max	0.067 max
t	0.94 max	0.037 max

SOLDERING PAD



	mm	inches
A	1.02	0.04
B	2.03	0.08
C	4.06	0.16
D	1.65	0.065

HOW TO ORDER

VC	1206	56	F	111	T	P
Varistor Chip	Case Size	Working Voltage	Energy Rating	Clamping Voltage	Packaging	Termination
		56 = 56Vdc	F = 0.7J	111 = 110V	D = 7" reel (1,000pcs) R = 7" reel (2,000pcs) T = 13" reel (10,000pcs)	P = Sn


VC120656F111TP

(1206, 56Vdc, 0.7J, 100A, 180pF, Sn Term)


Multilayer Chip Varistor Datasheet

TYPICAL CHARACTERISTICS


Temperature Derating (Energy, Current, Power)



Power Derating



Voltage / Current



S21

