

# VLAS080534C650DP

(0805, 34Vdc, 0.3J, 80A, 275pF, Sn Term)

Multilayer Chip Varistor Datasheet

## BASIC SPECIFICATION

Case Size [EIA]	0805
Operating Temperature	-55 to +125°C
Grade	Automotive & General
Qualification	AEC-Q200
Termination	Sn
RoHS	Yes
MSL Level	1
Packaging	T&R 7in (180mm)
Packaging Qty	1000 pcs



AEC-Q200  
Qualified



RoHS  
Compliant



Click for  
Online Data

## ELECTRICAL CHARACTERISTICS

DC Working Voltage	34 Vdc
AC Working Voltage	30 Vac
Breakdown Voltage [1mA DC]	39+13% V
Clamping Voltage [8x20μs]	65V @ 1A
Max Leakage Current [Vdc, 25°C]	10 μA
Transient Energy [10x1000μs]	0.3 J
Load Dump Energy [x10]	1 J
Peak Power [10x1000μs]	0 W
Peak Current Rating [8x20μs]	80 A
Typical Capacitance [1kHz, 0.5Vrms, 25°C]	275 pF
Capacitance Tolerance	+100/-50%
Jump Start Voltage [5min]	29 V
Power Dissipation	0.006 W

## DIMENSIONS



	mm	inches
L	2.01±0.20	0.079±0.008
W	1.25±0.20	0.049±0.008
T	1.02 max	0.040 max
t	0.71 max	0.028 max

## SOLDERING PAD



	mm	inches
A	1.02	0.04
B	1.02	0.04
C	3.05	0.12
D	1.27	0.05

## HOW TO ORDER


<b>VLAS</b>	<b>0805</b>	<b>34</b>	<b>C</b>	<b>650</b>	<b>D</b>	<b>P</b>
Varistor Low Clamp	Case Size	Working Voltage	Energy Rating	Clamping Voltage	Packaging	Termination
		34 = 34 Vdc	C = 0.3J	650 = 65V	D = 7" reel (1,000pcs) R = 7" reel (4,000pcs) T = 13" reel (10,000pcs)	P = Sn

## TYPICAL CHARACTERISTICS


Temperature Derating (Energy, Current, Power)



Power Derating



Voltage / Current



S21

