

NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

SpiCAT



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

Characteristics

Case Size	0805
Operating temperature	-55°C to +150°C
Resistance	3900 Ohm
Tolerance on Resistance (25°C)	$\pm 20\%$
B 25/85	3480K $\pm 3\%$
Maximum dissipation at 25°C	0.12 W
Thermal dissipation factor	2 mW/°C
Thermal time constant	5 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



RoHS
COMPLIANT

MSL 1
Pb Free
260°C



AEC-Q200
based qualification

Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
0805	2.0 ± 0.3	1.25 ± 0.2	1.3 max	0.2 min
	(0.079 ± 0.012)	(0.049 ± 0.008)	(0.051) max	(0.008) min



How to Order (Packaging options)

NB

Type

NB = Ni/Sn Term for lead free soldering

12

Size

12 = 0805

J0

Material Code

See Datasheet

0392

Resistance (Ohm)

2 Sig. Digits + Number of Zeros

M

Tolerance

H = $\pm 3\%*$
J = $\pm 5\%$
K = $\pm 10\%$
M = $\pm 20\%$

* For selected PNs

BB

Suffix: Packaging

BB = Cardboard tape (180mm reel, 4,000 pcs/reel)
BF = Cardboard tape (180mm reel, 2,000 pcs/reel)
BD = Cardboard tape (330mm reel, 10,000 pcs/reel)
-- = Bulk (5000 pcs/bag)

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

Material Table

J0 (B25/85 = 3480K $\pm 3\%$)

T (°C)	R(T) / R25	TF (%)	α (%/°C)
-55	51.75	20.47	-6.23
-50	37.98	17.69	-6.03
-45	28.15	15.21	-5.84
-40	21.07	13.00	-5.65
-35	15.91	11.04	-5.48
-30	12.13	9.31	-5.31
-25	9.321	7.77	-5.15
-20	7.222	6.41	-4.99
-15	5.640	5.22	-4.84
-10	4.438	4.18	-4.69
-5	3.517	3.27	-4.55
0	2.807	2.48	-4.42
5	2.255	1.80	-4.29
10	1.824	1.22	-4.17
15	1.484	0.73	-4.05
20	1.215	0.33	-3.93
25	1.000	0.00	-3.82
30	0.8278	0.32	-3.71
35	0.6889	0.68	-3.61
40	0.5763	1.08	-3.51
45	0.4845	1.51	-3.41
50	0.4092	1.98	-3.32
55	0.3472	2.47	-3.23
60	0.2960	2.99	-3.15
65	0.2533	3.53	-3.06
70	0.2177	4.09	-2.98
75	0.1879	4.67	-2.90
80	0.1628	5.26	-2.83
85	0.1415	5.87	-2.76
90	0.1235	6.48	-2.69
95	0.1081	7.11	-2.62
100	0.0950	7.74	-2.55
105	0.0837	8.38	-2.49
110	0.0740	9.03	-2.43
115	0.0656	9.68	-2.37
120	0.0584	10.33	-2.31
125	0.0521	10.99	-2.26
130	0.0466	11.65	-2.21
135	0.0417	12.31	-2.15
140	0.0375	12.97	-2.10
145	0.0338	13.63	-2.06
150	0.0305	14.29	-2.01

B25/50	B25/75	B25/85	B25/100	B Tol
3443 K	3471 K	3480 K	3492 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
120,139	201,830	283,520
92,291	148,115	203,939
71,134	109,791	148,448
55,051	82,170	109,289
42,798	62,067	81,335
33,436	47,298	61,160
26,257	36,352	46,446
20,727	28,167	35,607
16,449	21,997	27,545
13,123	17,308	21,493
10,526	13,718	16,909
8,487.1	10,948	13,409
6,878.7	8,796.2	10,714
5,603.5	7,113.0	8,622.4
4,587.6	5,787.6	6,987.5
3,774.3	4,737.3	5,700.4
3,120.0	3,900.0	4,680.0
2,572.5	3,228.5	3,884.4
2,131.2	2,686.8	3,242.4
1,773.8	2,247.6	2,721.3
1,482.9	1,889.4	2,295.9
1,245.2	1,596.0	1,946.7
1,049.9	1,354.3	1,658.6
888.9	1,154.3	1,419.7
755.5	988.0	1,220.5
644.6	849.2	1,053.8
552.0	732.8	913.6
474.4	634.8	795.2
409.2	551.9	694.7
354.1	481.6	609.1
307.4	421.7	536.0
267.7	370.5	473.2
233.8	326.5	419.2
204.9	288.7	372.5
180.0	256.0	332.0
158.6	227.7	296.7
140.1	203.0	266.0
124.1	181.6	239.0
110.2	162.8	215.4
98.1	146.4	194.6
87.5	131.9	176.2
78.3	119.1	160.0