

## NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

**SpiCAT**



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

## Characteristics

Case Size	0805
Operating temperature	-55°C to +150°C
Resistance	5000 Ohm
Tolerance on Resistance (25°C)	$\pm 5\%$
B 25/85	3480K $\pm 3\%$
Maximum dissipation at 25°C	0.12 W
Thermal dissipation factor	2 mW/°C
Thermal time constant	5 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



RoHS  
COMPLIANT

MSL 1  
Pb Free  
260°C



AEC-Q200  
based qualification

## Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
0805	2.0 $\pm 0.3$	1.25 $\pm 0.2$	1.3 max	0.2 min
	(0.079 $\pm 0.012$ )	(0.049 $\pm 0.008$ )	(0.051) max	(0.008) min



## How to Order (Packaging options)

<b>NB</b>	<b>12</b>	<b>J0</b>	<b>0502</b>	<b>J</b>	<b>BD</b>
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NB = Ni/Sn Term for lead free soldering	12 = 0805	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%^*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BB = Cardboard tape (180mm reel, 4,000 pcs/reel) BF = Cardboard tape (180mm reel, 2,000 pcs/reel) BD = Cardboard tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)

\* For selected PNs

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

## Material Table

J0 (B25/85 = 3480K $\pm 3\%$ )

T (°C)	R(T) / R25	TF (%)	$\alpha$ (%/°C)
-55	51.75	20.47	-6.23
-50	37.98	17.69	-6.03
-45	28.15	15.21	-5.84
-40	21.07	13.00	-5.65
-35	15.91	11.04	-5.48
-30	12.13	9.31	-5.31
-25	9.321	7.77	-5.15
-20	7.222	6.41	-4.99
-15	5.640	5.22	-4.84
-10	4.438	4.18	-4.69
-5	3.517	3.27	-4.55
0	2.807	2.48	-4.42
5	2.255	1.80	-4.29
10	1.824	1.22	-4.17
15	1.484	0.73	-4.05
20	1.215	0.33	-3.93
25	1.000	0.00	-3.82
30	0.8278	0.32	-3.71
35	0.6889	0.68	-3.61
40	0.5763	1.08	-3.51
45	0.4845	1.51	-3.41
50	0.4092	1.98	-3.32
55	0.3472	2.47	-3.23
60	0.2960	2.99	-3.15
65	0.2533	3.53	-3.06
70	0.2177	4.09	-2.98
75	0.1879	4.67	-2.90
80	0.1628	5.26	-2.83
85	0.1415	5.87	-2.76
90	0.1235	6.48	-2.69
95	0.1081	7.11	-2.62
100	0.0950	7.74	-2.55
105	0.0837	8.38	-2.49
110	0.0740	9.03	-2.43
115	0.0656	9.68	-2.37
120	0.0584	10.33	-2.31
125	0.0521	10.99	-2.26
130	0.0466	11.65	-2.21
135	0.0417	12.31	-2.15
140	0.0375	12.97	-2.10
145	0.0338	13.63	-2.06
150	0.0305	14.29	-2.01

B25/50	B25/75	B25/85	B25/100	B Tol
3443 K	3471 K	3480 K	3492 K	$\pm 3\%$

R Min ( $\Omega$ )	R Nom ( $\Omega$ )	R Max ( $\Omega$ )
192,838	258,756	324,674
146,806	189,891	232,977
112,312	140,758	169,205
86,380	105,346	124,312
66,806	79,573	92,340
51,963	60,639	69,315
40,653	46,604	52,556
31,990	36,111	40,233
25,318	28,201	31,084
20,153	22,190	24,226
16,133	17,587	19,041
12,986	14,036	15,085
10,510	11,277	12,044
8,551.9	9,119.2	9,686.5
6,994.6	7,420.0	7,845.4
5,749.8	6,073.5	6,397.2
4,750.0	5,000.0	5,250.0
3,919.0	4,139.1	4,359.1
3,249.1	3,444.7	3,640.2
2,706.3	2,881.5	3,056.6
2,264.6	2,422.3	2,580.1
1,903.3	2,046.1	2,188.9
1,606.5	1,736.2	1,866.0
1,361.6	1,479.8	1,598.1
1,158.6	1,266.7	1,374.8
989.7	1,088.7	1,187.7
848.7	939.5	1,030.4
730.3	813.9	897.4
630.7	707.6	784.5
546.6	617.4	688.3
475.2	540.6	606.1
414.4	475.0	535.5
362.6	418.6	474.6
318.2	370.1	422.0
280.0	328.2	376.4
247.1	291.9	336.6
218.7	260.3	301.9
194.0	232.8	271.6
172.6	208.7	244.9
153.9	187.6	221.4
137.6	169.1	200.6
123.3	152.7	182.2