

VCLD08LC18A500RB

(0805, 18Vdc, 0.1J, 30A, 80pF, SnPb)

Multilayer Chip Varistor Datasheet

BASIC SPECIFICATION

Case Size [EIA]	0805
Operating Temperature	-55 to +125°C
Grade	General
Termination	SnPb
RoHS	No
MSL Level	1
Packaging	T&R 7in (180mm)
Packaging Qty	4000 pcs



Non
RoHS



Click for
Online Data

ELECTRICAL CHARACTERISTICS

DC Working Voltage	18 Vdc
AC Working Voltage	14 Vac
Breakdown Voltage [1mA DC]	25-45 V
Clamping Voltage [8x20μs]	50V @ 1A
Max Leakage Current [Vdc, 25°C]	10 μA
Transient Energy [10x1000μs]	0.1 J
Peak Power [10x1000μs]	75 W
Peak Current Rating [8x20μs]	30 A
Typical Capacitance [1MHz, 0.5Vrms, 25°C]	80 pF
Capacitance Tolerance	+100/-50%

DIMENSIONS



	mm	inches
L	2.01±0.20	0.079±0.008
W	1.25±0.20	0.049±0.008
T	1.02 max	0.040 max
t	0.71 max	0.028 max

SOLDERING PAD



	mm	inches
A	1.02	0.04
B	1.02	0.04
C	3.05	0.12
D	1.27	0.05

HOW TO ORDER

VCLD	08	LC	18	A	500	R	B
Varistor Chip SnPb	Case Size 08 = 0805	Low Cap	Working Voltage 18 = 18Vdc	Energy Rating A = 0.1J	Clamping Voltage 500 = 50V	Packaging D = 7" reel (1,000pcs) R = 7" reel (4,000pcs) T = 13" reel (10,000pcs)	Termination B = SnPb (5% Pb min)

VCLD08LC18A500RB

(0805, 18Vdc, 0.1J, 30A, 80pF, SnPb)


Multilayer Chip Varistor Datasheet

TYPICAL CHARACTERISTICS


Temperature Derating (Energy, Current, Power)



Power Derating



Voltage / Current



S21

