

# VGAH222022Y490TP

(2220, 22Vdc, 6.8J, 1200A, 12000pF, Sn Term)

Multilayer Chip Varistor Datasheet



## BASIC SPECIFICATION

Case Size [EIA]	2220
Operating Temperature	-55 to +150°C
Grade	Automotive & General
Qualification	AEC-Q200
Termination	Sn
RoHS	Yes
MSL Level	1
Packaging	T&R 13in (330mm)
Packaging Qty	4000 pcs



AEC-Q200  
Qualified



RoHS  
Compliant




Click for  
Online Data

## ELECTRICAL CHARACTERISTICS


DC Working Voltage	22 Vdc
AC Working Voltage	17 Vac
Breakdown Votage [1mA DC]	30±10% V
Clamping Voltage [8x20µs]	49V @ 10A
Max Leakage Current [Vdc, 25°C]	15 µA
Transient Energy [10x1000µs]	6.8 J
Load Dump Energy [x10]	25 J
Peak Power [10x1000µs]	5120 W
Peak Current Rating [8x20µs]	1200 A
Typical Capacitance [1kHz, 0.5Vrms, 25°C]	12000 pF
Capacitance Tolerance	+100/-50%
Jump Start Voltage [5min]	27.5 V
Power Dissipation	0.03 W

## DIMENSIONS



	mm	inches
L	5.70±0.40	0.224±0.016
W	5.00±0.40	0.197±0.016
T	2.5 max	0.098 max
t	1.00 max	0.039 max

## SOLDERING PAD




	mm	inches
A	1.70	0.067
B	4	0.158
C	7.4	0.291
D	5.4	0.213

## HOW TO ORDER


<b>VGAH</b>	<b>2220</b>	<b>22</b>	<b>Y</b>	<b>490</b>	<b>T</b>	<b>P</b>
Varistor Glass Encapsulated 150°C	Case Size	Working Voltage	Energy Rating	Clamping Voltage	Packaging	Termination
		22 = 22 Vdc	Y = 6.8J	490 = 49V	D = 7" reel (1,000pcs) T = 13" reel (4,000pcs)	P = Sn

## TYPICAL CHARACTERISTICS


Temperature Derating (Energy, Current, Power)




Temperature Derating (Working Voltage)




Power Derating



Voltage / Current



S21



NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.