


## NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

**SpiCAT**



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

## Characteristics

Case Size	0805
Operating temperature	-55°C to +150°C
Resistance	33 kOhm
Tolerance on Resistance (25°C)	$\pm 10\%$
B 25/85	3950K $\pm 3\%$
Maximum dissipation at 25°C	0.12 W
Thermal dissipation factor	2 mW/°C
Thermal time constant	5 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



MSL 1  
Pb Free  
260°C




AEC-Q200  
based qualification

## Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
0805	2.0 $\pm 0.3$	1.25 $\pm 0.2$	1.3 max	0.2 min
	(0.079 $\pm 0.012$ )	(0.049 $\pm 0.008$ )	(0.051) max	(0.008) min



## How to Order (Packaging options)

<b>NB</b>	<b>12</b>	<b>M0</b>	<b>0333</b>	<b>K</b>	<b>BB</b>
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NB = Ni/Sn Term for lead free soldering	12 = 0805	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%^*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BB = Cardboard tape (180mm reel, 4,000 pcs/reel) BF = Cardboard tape (180mm reel, 2,000 pcs/reel) BD = Cardboard tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)

\* For selected PNs

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

## Material Table

**M0 (B25/85 = 3950K $\pm 3\%$ )**

T (°C)	R(T) / R25	TF (%)	$\alpha$ (%/°C)
-55	99.59	15.64	-7.42
-50	68.97	14.25	-7.16
-45	48.40	12.94	-6.91
-40	34.38	11.69	-6.67
-35	24.71	10.51	-6.45
-30	17.97	9.39	-6.23
-25	13.20	8.33	-6.02
-20	9.804	7.31	-5.82
-15	7.352	6.35	-5.63
-10	5.565	5.43	-5.45
-5	4.251	4.55	-5.28
0	3.275	3.70	-5.11
5	2.544	2.90	-4.95
10	1.992	2.13	-4.80
15	1.572	1.39	-4.65
20	1.249	0.68	-4.51
25	1.000	0.00	-4.38
30	0.8057	0.66	-4.25
35	0.6534	1.30	-4.12
40	0.5331	1.92	-4.00
45	0.4376	2.53	-3.89
50	0.3612	3.12	-3.77
55	0.2998	3.70	-3.67
60	0.2501	4.26	-3.57
65	0.2097	4.81	-3.47
70	0.1767	5.35	-3.37
75	0.1496	5.87	-3.28
80	0.1272	6.38	-3.19
85	0.1087	6.88	-3.11
90	0.0932	7.37	-3.03
95	0.0803	7.84	-2.95
100	0.0694	8.31	-2.87
105	0.0602	8.76	-2.80
110	0.0524	9.21	-2.73
115	0.0458	9.64	-2.66
120	0.0402	10.07	-2.60
125	0.0353	10.48	-2.53
130	0.0312	10.89	-2.47
135	0.0276	11.29	-2.41
140	0.0245	11.68	-2.36
145	0.0218	12.06	-2.30
150	0.0194	12.43	-2.25

B25/50	B25/75	B25/85	B25/100	B Tol
3925 K	3944 K	3950 K	3958 K	$\pm 3\%$

R Min ( $\Omega$ )	R Nom ( $\Omega$ )	R Max ( $\Omega$ )
2,443,896	3,286,477	4,129,057
1,724,173	2,276,156	2,828,139
1,230,707	1,597,038	1,963,370
888,388	1,134,518	1,380,648
648,232	815,540	982,848
477,914	592,906	707,897
355,861	435,725	515,590
267,515	323,534	379,553
202,948	242,611	282,273
155,322	183,652	211,982
119,877	140,282	160,687
93,272	108,084	122,895
73,136	83,967	94,798
57,777	65,751	73,725
45,970	51,879	57,787
36,828	41,232	45,636
29,700	33,000	36,300
23,755	26,589	29,423
19,125	21,561	23,997
15,495	17,592	19,690
12,630	14,439	16,248
10,355	11,919	13,483
8,537.1	9,892.3	11,247
7,076.3	8,253.5	9,430.7
5,895.9	6,921.0	7,946.2
4,936.9	5,832.0	6,727.0
4,153.7	4,937.2	5,720.8
3,510.8	4,198.6	4,886.4
2,980.7	3,586.0	4,191.3
2,541.4	3,075.5	3,609.7
2,175.8	2,648.4	3,120.9
1,870.2	2,289.4	2,708.5
1,613.7	1,986.4	2,359.1
1,397.6	1,729.8	2,062.0
1,214.7	1,511.5	1,808.4
1,059.3	1,325.2	1,591.2
926.9	1,165.7	1,404.4
813.7	1,028.5	1,243.4
716.5	910.3	1,104.0
632.8	807.9	983.1
560.5	719.1	877.8
497.9	641.8	785.8