

VLAS080530D570RP

(0805, 30Vdc, 0.4J, 125A, 275pF, Sn Term)

Multilayer Chip Varistor Datasheet

BASIC SPECIFICATION

Case Size [EIA]	0805
Operating Temperature	-55 to +125°C
Grade	Automotive & General
Qualification	AEC-Q200
Termination	Sn
RoHS	Yes
MSL Level	1
Packaging	T&R 7in (180mm)
Packaging Qty	4000 pcs



AEC-Q200
Qualified



RoHS
Compliant



Click for
Online Data

ELECTRICAL CHARACTERISTICS

DC Working Voltage	30 Vdc
AC Working Voltage	21 Vac
Breakdown Voltage [1mA DC]	34+13% V
Clamping Voltage [8x20μs]	57V @ 1A
Max Leakage Current [Vdc, 25°C]	15 μA
Transient Energy [10x1000μs]	0.4 J
Load Dump Energy [x10]	0.6 J
Peak Power [10x1000μs]	0 W
Peak Current Rating [8x20μs]	125 A
Typical Capacitance [1kHz, 0.5Vrms, 25°C]	275 pF
Capacitance Tolerance	+100/-50%
Jump Start Voltage [5min]	29 V
Power Dissipation	0.008 W

DIMENSIONS



	mm	inches
L	2.01±0.20	0.079±0.008
W	1.25±0.20	0.049±0.008
T	1.02 max	0.040 max
t	0.71 max	0.028 max

SOLDERING PAD



	mm	inches
A	1.02	0.04
B	1.02	0.04
C	3.05	0.12
D	1.27	0.05

HOW TO ORDER

VLAS	0805	30	D	570	R	P
Varistor Low Clamp	Case Size	Working Voltage	Energy Rating	Clamping Voltage	Packaging	Termination
		30 = 30 Vdc	D = 0.4J	570 = 57V	D = 7" reel (1,000pcs) R = 7" reel (4,000pcs) T = 13" reel (10,000pcs)	P = Sn

VLAS080530D570RP

(0805, 30Vdc, 0.4J, 125A, 275pF, Sn Term)

Multilayer Chip Varistor Datasheet



TYPICAL CHARACTERISTICS

