

BASIC SPECIFICATION


Case Size [EIA]	0603
Operating Temperature	-55 to +175°C
Grade	Automotive & General
Qualification	AEC-Q200
Termination	Sn
RoHS	Yes
MSL Level	1
Packaging	T&R 13in (330mm)
Packaging Qty	10000 pcs



ELECTRICAL CHARACTERISTICS


DC Working Voltage	14 Vdc
AC Working Voltage	10 Vac
Breakdown Votage [1mA DC]	18.5±12% V
Clamping Voltage [8x20µs]	32V @ 1A
Max Leakage Current [Vdc, 25°C]	10 µA
Transient Energy [10x1000µs]	0.1 J
Load Dump Energy [x10]	-
Peak Power [10x1000µs]	75 W
Peak Current Rating [8x20µs]	50 A
Typical Capacitance [1kHz, 0.5Vrms, 25°C]	400 pF
Capacitance Tolerance	+100/-50%
Jump Start Voltage [5min]	20 V
Power Dissipation	0.03 W

DIMENSIONS



	mm	inches
L	1.60±0.15	0.063±0.006
W	0.80±0.15	0.031±0.006
T	0.9 max	0.035 max
t	0.35±0.15	0.014±0.006

SOLDERING PAD




	mm	inches
A	0.89	0.035
B	0.76	0.03
C	2.54	0.1
D	0.76	0.03

HOW TO ORDER

VTA7	0603	14	A	300	T	P
Varistor 175°C	Case Size	Working Voltage	Energy Rating	Clamping Voltage	Packaging	Termination
		14 = 14 Vdc	A = 0.1J	300 = 32V	D = 7" reel (1,000pcs) R = 7" reel (4,000pcs) T = 13" reel (10,000pcs)	P = Sn

TYPICAL CHARACTERISTICS



NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.