

NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

SpiCAT



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

Characteristics

Case Size	0805
Operating temperature	-55°C to +150°C
Resistance	18 kOhm
Tolerance on Resistance (25°C)	$\pm 3\%$
B 25/85	3950K $\pm 3\%$
Maximum dissipation at 25°C	0.12 W
Thermal dissipation factor	2 mW/°C
Thermal time constant	5 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



RoHS
COMPLIANT

MSL 1
Pb Free
260°C



AEC-Q200
based qualification







Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
0805	2.0 ± 0.3	1.25 ± 0.2	1.3 max	0.2 min
	(0.079 ± 0.012)	(0.049 ± 0.008)	(0.051) max	(0.008) min



How to Order (Packaging options)

NB  Type NB = Ni/Sn Term for lead free soldering	12  Size 12 = 0805	M0  Material Code See Datasheet	0183  Resistance (Ohm) 2 Sig. Digits + Number of Zeros	H  Tolerance H = $\pm 3\%$ * J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BF  Suffix: Packaging BB = Cardboard tape (180mm reel, 4,000 pcs/reel) BF = Cardboard tape (180mm reel, 2,000 pcs/reel) BD = Cardboard tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)
--	--	---	--	---	---

* For selected PNs

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

Material Table

M0 (B25/85 = 3950K $\pm 3\%$)

T (°C)	R(T) / R25	TF (%)	α (%/°C)
-55	99.59	15.64	-7.42
-50	68.97	14.25	-7.16
-45	48.40	12.94	-6.91
-40	34.38	11.69	-6.67
-35	24.71	10.51	-6.45
-30	17.97	9.39	-6.23
-25	13.20	8.33	-6.02
-20	9.804	7.31	-5.82
-15	7.352	6.35	-5.63
-10	5.565	5.43	-5.45
-5	4.251	4.55	-5.28
0	3.275	3.70	-5.11
5	2.544	2.90	-4.95
10	1.992	2.13	-4.80
15	1.572	1.39	-4.65
20	1.249	0.68	-4.51
25	1.000	0.00	-4.38
30	0.8057	0.66	-4.25
35	0.6534	1.30	-4.12
40	0.5331	1.92	-4.00
45	0.4376	2.53	-3.89
50	0.3612	3.12	-3.77
55	0.2998	3.70	-3.67
60	0.2501	4.26	-3.57
65	0.2097	4.81	-3.47
70	0.1767	5.35	-3.37
75	0.1496	5.87	-3.28
80	0.1272	6.38	-3.19
85	0.1087	6.88	-3.11
90	0.0932	7.37	-3.03
95	0.0803	7.84	-2.95
100	0.0694	8.31	-2.87
105	0.0602	8.76	-2.80
110	0.0524	9.21	-2.73
115	0.0458	9.64	-2.66
120	0.0402	10.07	-2.60
125	0.0353	10.48	-2.53
130	0.0312	10.89	-2.47
135	0.0276	11.29	-2.41
140	0.0245	11.68	-2.36
145	0.0218	12.06	-2.30
150	0.0194	12.43	-2.25

B25/50	B25/75	B25/85	B25/100	B Tol
3925 K	3944 K	3950 K	3958 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
1,458,518	1,792,624	2,126,729
1,027,366	1,241,540	1,455,713
732,273	871,112	1,009,951
527,893	618,828	709,763
384,720	444,840	504,960
283,319	323,403	363,487
210,743	237,668	264,594
158,270	176,473	194,676
119,962	132,333	144,704
91,733	100,174	108,615
70,744	76,517	82,291
55,002	58,955	62,907
43,099	45,800	48,502
34,025	35,864	37,703
27,055	28,297	29,539
21,663	22,490	23,318
17,460	18,000	18,540
13,973	14,503	15,033
11,255	11,761	12,266
9,123.5	9,595.8	10,068
7,440.4	7,875.9	8,311.5
6,103.2	6,501.2	6,899.2
5,034.3	5,395.8	5,757.3
4,174.9	4,501.9	4,828.9
3,480.2	3,775.1	4,070.0
2,915.5	3,181.1	3,446.6
2,454.1	2,693.0	2,931.9
2,075.3	2,290.2	2,505.0
1,762.7	1,956.0	2,149.3
1,503.7	1,677.6	1,851.5
1,287.9	1,444.6	1,601.2
1,107.5	1,248.7	1,390.0
956.1	1,083.5	1,210.9
828.4	943.5	1,058.7
720.3	824.5	928.7
628.4	722.9	817.3
550.1	635.8	721.5
483.1	561.0	638.9
425.6	496.5	567.4
376.0	440.7	505.4
333.2	392.3	451.3
296.1	350.1	404.1