

NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

SpiCAT



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

Characteristics

Case Size	1206
Operating temperature	-55°C to +150°C
Resistance	5600 Ohm
Tolerance on Resistance (25°C)	$\pm 3\%$
B 25/85	3480K $\pm 3\%$
Maximum dissipation at 25°C	0.24 W
Thermal dissipation factor	4 mW/°C
Thermal time constant	7 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



MSL 1
Pb Free
260°C



AEC-Q200
based qualification

Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
1206	3.2 ± 0.4	1.6 ± 0.25	1.5 max	0.2 min
	(0.126 ± 0.016)	(0.063 ± 0.01)	(0.059) max	(0.008) min



How to Order (Packaging options)

NB	20	J0	0562	H	BE
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NB = Ni/Sn Term for lead free soldering	20 = 1206	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BA = Plastic tape (180mm reel, 3,000 pcs/reel) BE = Plastic tape (180mm reel, 1,500 pcs/reel) BC = Plastic tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)
				* For selected PNs	

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

Material Table

J0 (B25/85 = 3480K $\pm 3\%$)

T (°C)	R(T) / R25	TF (%)	α (%/°C)
-55	51.75	20.47	-6.23
-50	37.98	17.69	-6.03
-45	28.15	15.21	-5.84
-40	21.07	13.00	-5.65
-35	15.91	11.04	-5.48
-30	12.13	9.31	-5.31
-25	9.321	7.77	-5.15
-20	7.222	6.41	-4.99
-15	5.640	5.22	-4.84
-10	4.438	4.18	-4.69
-5	3.517	3.27	-4.55
0	2.807	2.48	-4.42
5	2.255	1.80	-4.29
10	1.824	1.22	-4.17
15	1.484	0.73	-4.05
20	1.215	0.33	-3.93
25	1.000	0.00	-3.82
30	0.8278	0.32	-3.71
35	0.6889	0.68	-3.61
40	0.5763	1.08	-3.51
45	0.4845	1.51	-3.41
50	0.4092	1.98	-3.32
55	0.3472	2.47	-3.23
60	0.2960	2.99	-3.15
65	0.2533	3.53	-3.06
70	0.2177	4.09	-2.98
75	0.1879	4.67	-2.90
80	0.1628	5.26	-2.83
85	0.1415	5.87	-2.76
90	0.1235	6.48	-2.69
95	0.1081	7.11	-2.62
100	0.0950	7.74	-2.55
105	0.0837	8.38	-2.49
110	0.0740	9.03	-2.43
115	0.0656	9.68	-2.37
120	0.0584	10.33	-2.31
125	0.0521	10.99	-2.26
130	0.0466	11.65	-2.21
135	0.0417	12.31	-2.15
140	0.0375	12.97	-2.10
145	0.0338	13.63	-2.06
150	0.0305	14.29	-2.01

B25/50	B25/75	B25/85	B25/100	B Tol
3443 K	3471 K	3480 K	3492 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
221,775	289,807	357,839
168,676	212,678	256,680
128,942	157,649	186,356
99,105	117,987	136,870
76,605	89,121	101,638
59,557	67,916	76,274
46,575	52,197	57,819
36,637	40,445	44,253
28,988	31,585	34,182
23,069	24,853	26,636
18,463	19,697	20,932
14,859	15,720	16,581
12,024	12,630	13,237
9,782.4	10,213	10,645
8,000.1	8,310.4	8,620.6
6,575.9	6,802.3	7,028.8
5,432.0	5,600.0	5,768.0
4,482.0	4,635.7	4,789.5
3,716.1	3,858.0	3,999.9
3,095.7	3,227.3	3,358.9
2,590.6	2,713.0	2,835.5
2,177.5	2,291.6	2,405.7
1,838.1	1,944.6	2,051.0
1,558.1	1,657.4	1,756.7
1,326.0	1,418.7	1,511.4
1,132.9	1,219.4	1,305.9
971.5	1,052.3	1,133.0
836.2	911.5	986.8
722.3	792.5	862.8
626.0	691.5	757.1
544.3	605.5	666.7
474.8	532.0	589.1
415.5	468.8	522.2
364.7	414.5	464.4
321.0	367.6	414.2
283.3	326.9	370.5
250.8	291.5	332.3
222.5	260.7	298.9
198.0	233.8	269.6
176.6	210.2	243.7
157.9	189.4	220.9
141.5	171.1	200.7