


NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

SpiCAT



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

Characteristics

Case Size	1206
Operating temperature	-55°C to +150°C
Resistance	6800 Ohm
Tolerance on Resistance (25°C)	$\pm 3\%$
B 25/85	3480K $\pm 3\%$
Maximum dissipation at 25°C	0.24 W
Thermal dissipation factor	4 mW/°C
Thermal time constant	7 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



MSL 1
Pb Free
260°C




AEC-Q200
based qualification

Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
1206	3.2 ± 0.4 (0.126 ± 0.016)	1.6 ± 0.25 (0.063 ± 0.01)	1.5 max (0.059) max	0.2 min (0.008) min



How to Order (Packaging options)

NB	20	J0	0682	H	BE
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NB = Ni/Sn Term for lead free soldering	20 = 1206	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BA = Plastic tape (180mm reel, 3,000 pcs/reel) BE = Plastic tape (180mm reel, 1,500 pcs/reel) BC = Plastic tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)
				* For selected PNs	

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

Material Table

J0 (B25/85 = 3480K $\pm 3\%$)

T (°C)	R(T) / R25	TF (%)	α (%/°C)
-55	51.75	20.47	-6.23
-50	37.98	17.69	-6.03
-45	28.15	15.21	-5.84
-40	21.07	13.00	-5.65
-35	15.91	11.04	-5.48
-30	12.13	9.31	-5.31
-25	9.321	7.77	-5.15
-20	7.222	6.41	-4.99
-15	5.640	5.22	-4.84
-10	4.438	4.18	-4.69
-5	3.517	3.27	-4.55
0	2.807	2.48	-4.42
5	2.255	1.80	-4.29
10	1.824	1.22	-4.17
15	1.484	0.73	-4.05
20	1.215	0.33	-3.93
25	1.000	0.00	-3.82
30	0.8278	0.32	-3.71
35	0.6889	0.68	-3.61
40	0.5763	1.08	-3.51
45	0.4845	1.51	-3.41
50	0.4092	1.98	-3.32
55	0.3472	2.47	-3.23
60	0.2960	2.99	-3.15
65	0.2533	3.53	-3.06
70	0.2177	4.09	-2.98
75	0.1879	4.67	-2.90
80	0.1628	5.26	-2.83
85	0.1415	5.87	-2.76
90	0.1235	6.48	-2.69
95	0.1081	7.11	-2.62
100	0.0950	7.74	-2.55
105	0.0837	8.38	-2.49
110	0.0740	9.03	-2.43
115	0.0656	9.68	-2.37
120	0.0584	10.33	-2.31
125	0.0521	10.99	-2.26
130	0.0466	11.65	-2.21
135	0.0417	12.31	-2.15
140	0.0375	12.97	-2.10
145	0.0338	13.63	-2.06
150	0.0305	14.29	-2.01

B25/50	B25/75	B25/85	B25/100	B Tol
3443 K	3471 K	3480 K	3492 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
269,298	351,908	434,519
204,821	258,252	311,683
156,573	191,431	226,290
120,342	143,270	166,199
93,020	108,219	123,418
72,319	82,469	92,619
56,556	63,382	70,209
44,488	49,112	53,735
35,200	38,353	41,507
28,012	30,178	32,344
22,419	23,918	25,417
18,043	19,089	20,134
14,601	15,337	16,073
11,879	12,402	12,926
9,714.4	10,091	10,468
7,985.0	8,260.0	8,534.9
6,596.0	6,800.0	7,004.0
5,442.4	5,629.1	5,815.8
4,512.4	4,684.7	4,857.0
3,759.0	3,918.8	4,078.7
3,145.7	3,294.4	3,443.1
2,644.1	2,782.7	2,921.3
2,232.0	2,361.3	2,490.5
1,892.0	2,012.6	2,133.2
1,610.2	1,722.7	1,835.3
1,375.7	1,480.7	1,585.7
1,179.7	1,277.7	1,375.7
1,015.4	1,106.8	1,198.3
877.0	962.4	1,047.7
760.1	839.7	919.4
660.9	735.3	809.6
576.6	645.9	715.3
504.5	569.3	634.1
442.8	503.3	563.9
389.7	446.3	502.9
344.0	396.9	449.9
304.5	354.0	403.5
270.2	316.6	363.0
240.4	283.9	327.3
214.4	255.2	295.9
191.7	230.0	268.2
171.8	207.7	243.6