

## NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

**SpiCAT**



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

## Characteristics

Case Size	1206
Operating temperature	-55°C to +150°C
Resistance	12 kOhm
Tolerance on Resistance (25°C)	$\pm 10\%$
B 25/85	3630K $\pm 3\%$
Maximum dissipation at 25°C	0.24 W
Thermal dissipation factor	4 mW/°C
Thermal time constant	7 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



MSL 1  
Pb Free  
260°C



AEC-Q200  
based qualification

## Dimensions WWWW

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
1206	3.2 $\pm 0.4$	1.6 $\pm 0.25$	1.5 max	0.2 min
	(0.126 $\pm 0.016$ )	(0.063 $\pm 0.01$ )	(0.059) max	(0.008) min



## How to Order (Packaging options)

<b>NB</b>	<b>20</b>	<b>K0</b>	<b>0123</b>	<b>K</b>	<b>BA</b>
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NB = Ni/Sn Term for lead free soldering	20 = 1206	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BA = Plastic tape (180mm reel, 3,000 pcs/reel) BE = Plastic tape (180mm reel, 1,500 pcs/reel) BC = Plastic tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)
				* For selected PNs	

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

## Material Table

K0 (B25/85 = 3630K $\pm 3\%$ )

T (°C)	R(T) / R25	TF (%)	$\alpha$ (%/°C)
-55	56.27	21.36	-6.25
-50	41.22	18.45	-6.06
-45	30.48	15.86	-5.89
-40	22.74	13.56	-5.71
-35	17.11	11.52	-5.55
-30	12.98	9.71	-5.39
-25	9.931	8.10	-5.24
-20	7.655	6.69	-5.09
-15	5.945	5.45	-4.95
-10	4.651	4.36	-4.81
-5	3.663	3.41	-4.67
0	2.905	2.58	-4.54
5	2.319	1.88	-4.42
10	1.862	1.27	-4.30
15	1.505	0.77	-4.18
20	1.223	0.34	-4.07
25	1.000	0.00	-3.96
30	0.8219	0.33	-3.85
35	0.6792	0.71	-3.75
40	0.5641	1.12	-3.65
45	0.4708	1.58	-3.55
50	0.3949	2.07	-3.46
55	0.3327	2.58	-3.37
60	0.2816	3.12	-3.28
65	0.2393	3.69	-3.20
70	0.2043	4.27	-3.12
75	0.1751	4.87	-3.04
80	0.1506	5.49	-2.96
85	0.1301	6.12	-2.89
90	0.1128	6.76	-2.82
95	0.0981	7.41	-2.75
100	0.0856	8.07	-2.68
105	0.0750	8.74	-2.61
110	0.0659	9.42	-2.55
115	0.0581	10.09	-2.49
120	0.0514	10.78	-2.43
125	0.0455	11.46	-2.37
130	0.0405	12.15	-2.32
135	0.0361	12.84	-2.26
140	0.0323	13.53	-2.21
145	0.0289	14.22	-2.16
150	0.0260	14.91	-2.11

B25/50	B25/75	B25/85	B25/100	B Tol
3581 K	3618 K	3630 K	3646 K	$\pm 3\%$

R Min ( $\Omega$ )	R Nom ( $\Omega$ )	R Max ( $\Omega$ )
463,501	675,226	886,951
353,908	494,637	635,365
271,139	365,732	460,326
208,560	272,854	337,147
161,140	205,326	249,511
125,095	155,800	186,505
97,596	119,172	140,748
76,531	91,863	107,196
60,323	71,343	82,363
47,795	55,807	63,820
38,066	43,960	49,853
30,474	34,861	39,248
24,520	27,825	31,130
19,830	22,349	24,869
16,116	18,060	20,004
13,161	14,680	16,198
10,800	12,000	13,200
8,844.3	9,863.3	10,882
7,277.4	8,150.0	9,022.7
6,015.9	6,768.9	7,521.9
4,995.6	5,649.7	6,303.9
4,166.5	4,738.2	5,309.9
3,490.0	3,992.2	4,494.4
2,935.4	3,378.7	3,822.1
2,478.9	2,871.9	3,265.0
2,101.6	2,451.4	2,801.2
1,788.5	2,100.9	2,413.4
1,527.7	1,807.6	2,087.6
1,309.6	1,561.2	1,812.9
1,126.5	1,353.3	1,580.2
972.3	1,177.3	1,382.3
842.0	1,027.7	1,213.5
731.4	900.1	1,068.8
637.4	790.9	944.5
557.0	697.1	837.2
488.3	616.3	744.4
429.2	546.5	663.8
378.3	485.9	593.6
334.3	433.3	532.2
296.2	387.4	478.5
263.1	347.2	431.3
234.3	312.0	389.7