

## NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

**SpiCAT**



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

## Characteristics

Case Size	0805
Operating temperature	-55°C to +150°C
Resistance	56 kOhm
Tolerance on Resistance (25°C)	$\pm 10\%$
B 25/85	4080K $\pm 3\%$
Maximum dissipation at 25°C	0.12 W
Thermal dissipation factor	2 mW/°C
Thermal time constant	5 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



MSL 1  
Pb Free  
260°C



AEC-Q200  
based qualification

## Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
0805	2.0 $\pm 0.3$	1.25 $\pm 0.2$	1.3 max	0.2 min
	(0.079 $\pm 0.012$ )	(0.049 $\pm 0.008$ )	(0.051) max	(0.008) min



## How to Order (Packaging options)

<b>NB</b>	<b>12</b>	<b>N0</b>	<b>0563</b>	<b>K</b>	<b>BD</b>
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NB = Ni/Sn Term for lead free soldering	12 = 0805	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%^*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BB = Cardboard tape (180mm reel, 4,000 pcs/reel) BF = Cardboard tape (180mm reel, 2,000 pcs/reel) BD = Cardboard tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)

\* For selected PNs

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

## Material Table

**N0 (B25/85 = 4080K $\pm 3\%$ )**

T (°C)	R(T) / R25	TF (%)	$\alpha$ (%/°C)
-55	110.1	24.01	-7.50
-50	75.89	20.74	-7.25
-45	52.97	17.83	-7.01
-40	37.42	15.25	-6.78
-35	26.75	12.95	-6.56
-30	19.33	10.91	-6.35
-25	14.11	9.11	-6.14
-20	10.41	7.52	-5.95
-15	7.758	6.12	-5.76
-10	5.834	4.90	-5.58
-5	4.426	3.83	-5.41
0	3.387	2.91	-5.24
5	2.614	2.11	-5.08
10	2.033	1.43	-4.93
15	1.593	0.86	-4.78
20	1.258	0.39	-4.64
25	1.000	0.00	-4.51
30	0.8004	0.37	-4.37
35	0.6449	0.80	-4.25
40	0.5228	1.26	-4.13
45	0.4264	1.77	-4.01
50	0.3497	2.32	-3.90
55	0.2885	2.90	-3.79
60	0.2392	3.51	-3.68
65	0.1994	4.14	-3.58
70	0.1671	4.80	-3.49
75	0.1406	5.48	-3.39
80	0.1189	6.17	-3.30
85	0.1010	6.88	-3.22
90	0.0862	7.60	-3.13
95	0.0738	8.33	-3.05
100	0.0635	9.08	-2.97
105	0.0548	9.83	-2.90
110	0.0475	10.58	-2.83
115	0.0413	11.35	-2.76
120	0.0360	12.11	-2.69
125	0.0315	12.89	-2.62
130	0.0277	13.66	-2.56
135	0.0244	14.43	-2.50
140	0.0216	15.21	-2.44
145	0.0191	15.98	-2.38
150	0.0170	16.76	-2.33

B25/50	B25/75	B25/85	B25/100	B Tol
4049 K	4072 K	4080 K	4090 K	$\pm 3\%$

R Min ( $\Omega$ )	R Nom ( $\Omega$ )	R Max ( $\Omega$ )
4,068,794	6,165,451	8,262,109
2,943,385	4,249,804	5,556,223
2,140,806	2,966,457	3,792,108
1,566,641	2,095,746	2,624,851
1,154,049	1,497,782	1,841,515
855,982	1,082,326	1,308,669
639,378	790,436	941,494
480,981	583,155	685,328
364,396	434,439	504,482
278,016	326,685	375,354
213,588	247,868	282,149
165,211	189,691	214,171
128,647	146,372	164,096
100,830	113,844	126,858
79,532	89,221	98,910
63,122	70,437	77,753
50,400	56,000	61,600
40,175	44,824	49,473
32,213	36,112	40,010
25,977	29,275	32,573
21,065	23,876	26,687
17,172	19,585	21,998
14,071	16,155	18,239
11,588	13,397	15,207
9,588.4	11,168	12,747
7,971.1	9,355.7	10,740
6,656.4	7,875.1	9,093.8
5,582.7	6,659.4	7,736.2
4,701.8	5,656.5	6,611.2
3,976.0	4,825.2	5,674.5
3,375.4	4,133.1	4,890.9
2,876.4	3,554.5	4,232.5
2,460.2	3,068.6	3,677.0
2,111.6	2,658.9	3,206.3
1,818.6	2,312.3	2,805.9
1,571.5	2,017.7	2,464.0
1,362.3	1,766.6	2,170.9
1,184.6	1,551.8	1,918.9
1,033.2	1,367.3	1,701.3
903.8	1,208.4	1,513.0
792.8	1,071.0	1,349.3
697.3	952.0	1,206.7