


## NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

**SpiCAT**



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

## Characteristics

Case Size	1206
Operating temperature	-55°C to +150°C
Resistance	56 kOhm
Tolerance on Resistance (25°C)	$\pm 5\%$
B 25/85	4080K $\pm 3\%$
Maximum dissipation at 25°C	0.24 W
Thermal dissipation factor	4 mW/°C
Thermal time constant	7 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



MSL 1  
Pb Free  
260°C




AEC-Q200  
based qualification

## Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
1206	3.2 $\pm 0.4$	1.6 $\pm 0.25$	1.5 max	0.2 min
	(0.126 $\pm 0.016$ )	(0.063 $\pm 0.01$ )	(0.059) max	(0.008) min



## How to Order (Packaging options)

**NB**

Type

NB = Ni/Sn Term for lead free soldering

**20**

Size

20 = 1206

**N0**

Material Code

See Datasheet

**0563**

Resistance (Ohm)

2 Sig. Digits + Number of Zeros

**J**

Tolerance

H =  $\pm 3\%*$   
J =  $\pm 5\%$   
K =  $\pm 10\%$   
M =  $\pm 20\%$

\* For selected PNs

**BE**

Suffix: Packaging

BA = Plastic tape (180mm reel, 3,000 pcs/reel)  
BE = Plastic tape (180mm reel, 1,500 pcs/reel)  
BC = Plastic tape (330mm reel, 10,000 pcs/reel)  
-- = Bulk (5000 pcs/bag)

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

## Material Table

**N0 (B25/85 = 4080K $\pm 3\%$ )**

T (°C)	R(T) / R25	TF (%)	$\alpha$ (%/°C)
-55	110.1	24.01	-7.50
-50	75.89	20.74	-7.25
-45	52.97	17.83	-7.01
-40	37.42	15.25	-6.78
-35	26.75	12.95	-6.56
-30	19.33	10.91	-6.35
-25	14.11	9.11	-6.14
-20	10.41	7.52	-5.95
-15	7.758	6.12	-5.76
-10	5.834	4.90	-5.58
-5	4.426	3.83	-5.41
0	3.387	2.91	-5.24
5	2.614	2.11	-5.08
10	2.033	1.43	-4.93
15	1.593	0.86	-4.78
20	1.258	0.39	-4.64
25	1.000	0.00	-4.51
30	0.8004	0.37	-4.37
35	0.6449	0.80	-4.25
40	0.5228	1.26	-4.13
45	0.4264	1.77	-4.01
50	0.3497	2.32	-3.90
55	0.2885	2.90	-3.79
60	0.2392	3.51	-3.68
65	0.1994	4.14	-3.58
70	0.1671	4.80	-3.49
75	0.1406	5.48	-3.39
80	0.1189	6.17	-3.30
85	0.1010	6.88	-3.22
90	0.0862	7.60	-3.13
95	0.0738	8.33	-3.05
100	0.0635	9.08	-2.97
105	0.0548	9.83	-2.90
110	0.0475	10.58	-2.83
115	0.0413	11.35	-2.76
120	0.0360	12.11	-2.69
125	0.0315	12.89	-2.62
130	0.0277	13.66	-2.56
135	0.0244	14.43	-2.50
140	0.0216	15.21	-2.44
145	0.0191	15.98	-2.38
150	0.0170	16.76	-2.33

B25/50	B25/75	B25/85	B25/100	B Tol
4049 K	4072 K	4080 K	4090 K	$\pm 3\%$

R Min ( $\Omega$ )	R Nom ( $\Omega$ )	R Max ( $\Omega$ )
4,377,066	6,165,451	7,953,836
3,155,876	4,249,804	5,343,733
2,289,129	2,966,457	3,643,785
1,671,428	2,095,746	2,520,063
1,228,939	1,497,782	1,766,626
910,099	1,082,326	1,254,553
678,899	790,436	901,972
510,139	583,155	656,171
386,118	434,439	482,760
294,351	326,685	359,020
225,981	247,868	269,756
174,696	189,691	204,686
135,965	146,372	156,778
106,522	113,844	121,165
83,993	89,221	94,449
66,644	70,437	74,231
53,200	56,000	58,800
42,416	44,824	47,232
34,019	36,112	38,204
27,441	29,275	31,109
22,258	23,876	25,493
18,151	19,585	21,019
14,879	16,155	17,432
12,257	13,397	14,537
10,147	11,168	12,189
8,438.9	9,355.7	10,272
7,050.1	7,875.1	8,700.0
5,915.6	6,659.4	7,403.2
4,984.6	5,656.5	6,328.4
4,217.3	4,825.2	5,433.2
3,582.1	4,133.1	4,684.2
3,054.1	3,554.5	4,054.8
2,613.6	3,068.6	3,523.5
2,244.6	2,658.9	3,073.3
1,934.3	2,312.3	2,690.2
1,672.4	2,017.7	2,363.1
1,450.7	1,766.6	2,082.6
1,262.2	1,551.8	1,841.3
1,101.6	1,367.3	1,633.0
964.2	1,208.4	1,452.6
846.3	1,071.0	1,295.8
744.9	952.0	1,159.1