

NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

SpiCAT



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

Characteristics

Case Size	1206
Operating temperature	-55°C to +150°C
Resistance	120 kOhm
Tolerance on Resistance (25°C)	$\pm 5\%$
B 25/85	4220K $\pm 3\%$
Maximum dissipation at 25°C	0.24 W
Thermal dissipation factor	4 mW/°C
Thermal time constant	7 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



MSL 1
Pb Free
260°C



AEC-Q200
based qualification

Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
1206	3.2 ± 0.4	1.6 ± 0.25	1.5 max	0.2 min
	(0.126 ± 0.016)	(0.063 ± 0.01)	(0.059) max	(0.008) min



How to Order (Packaging options)

NB	20	P0	0124	J	BE
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NB = Ni/Sn Term for lead free soldering	20 = 1206	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BA = Plastic tape (180mm reel, 3,000 pcs/reel) BE = Plastic tape (180mm reel, 1,500 pcs/reel) BC = Plastic tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)
				* For selected PNs	

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

Material Table

P0 (B25/85 = 4220K $\pm 3\%$)

T (°C)	R(T) / R25	TF (%)	α (%/°C)
-55	121.4	24.83	-7.56
-50	83.35	21.45	-7.32
-45	57.92	18.44	-7.09
-40	40.72	15.77	-6.87
-35	28.95	13.39	-6.66
-30	20.80	11.29	-6.45
-25	15.10	9.42	-6.26
-20	11.07	7.78	-6.07
-15	8.197	6.33	-5.89
-10	6.123	5.07	-5.71
-5	4.615	3.96	-5.54
0	3.508	3.00	-5.38
5	2.688	2.18	-5.22
10	2.076	1.48	-5.07
15	1.616	0.89	-4.92
20	1.267	0.40	-4.78
25	1.000	0.00	-4.64
30	0.7949	0.38	-4.51
35	0.6359	0.82	-4.38
40	0.5120	1.31	-4.26
45	0.4148	1.84	-4.14
50	0.3379	2.40	-4.03
55	0.2769	3.00	-3.92
60	0.2281	3.63	-3.81
65	0.1890	4.28	-3.71
70	0.1573	4.96	-3.61
75	0.1316	5.66	-3.52
80	0.1106	6.38	-3.42
85	0.0934	7.11	-3.34
90	0.0792	7.86	-3.25
95	0.0674	8.62	-3.17
100	0.0577	9.39	-3.09
105	0.0495	10.16	-3.01
110	0.0427	10.95	-2.93
115	0.0369	11.74	-2.86
120	0.0320	12.53	-2.79
125	0.0279	13.33	-2.72
130	0.0244	14.13	-2.66
135	0.0214	14.93	-2.59
140	0.0188	15.73	-2.53
145	0.0166	16.53	-2.47
150	0.0147	17.33	-2.42

B25/50	B25/75	B25/85	B25/100	B Tol
4181 K	4211 K	4220 K	4232 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
10,220,755	14,565,769	18,910,782
7,355,969	10,001,639	12,647,310
5,321,259	6,950,879	8,580,499
3,871,901	4,886,899	5,901,897
2,835,173	3,474,212	4,113,252
2,089,847	2,496,447	2,903,047
1,550,990	1,812,399	2,073,808
1,159,051	1,328,865	1,498,678
872,177	983,651	1,095,125
660,851	734,817	808,783
504,163	553,792	603,421
387,227	420,921	454,616
299,391	322,556	345,722
232,987	249,132	265,276
182,467	193,886	205,304
143,791	151,997	160,203
114,000	120,000	126,000
90,247	95,383	100,520
71,871	76,314	80,757
57,567	61,443	65,318
46,369	49,771	53,173
37,552	40,553	43,554
30,571	33,229	35,888
25,015	27,377	29,740
20,569	22,674	24,780
16,994	18,875	20,756
14,105	15,789	17,473
11,760	13,270	14,780
9,846.9	11,204	12,561
8,279.4	9,501.4	10,723
6,989.7	8,091.7	9,193.7
5,924.0	6,919.5	7,915.0
5,039.8	5,940.6	6,841.4
4,303.3	5,119.7	5,936.2
3,687.4	4,428.6	5,169.9
3,170.6	3,844.6	4,518.5
2,735.3	3,349.1	3,962.9
2,367.3	2,927.2	3,487.1
2,055.2	2,566.7	3,078.2
1,789.7	2,257.7	2,725.7
1,563.0	1,991.9	2,420.8
1,369.0	1,762.6	2,156.2