

NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

SpiCAT



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

Characteristics

Case Size	1206
Operating temperature	-55°C to +150°C
Resistance	330 kOhm
Tolerance on Resistance (25°C)	$\pm 10\%$
B 25/85	4300K $\pm 3\%$
Maximum dissipation at 25°C	0.24 W
Thermal dissipation factor	4 mW/°C
Thermal time constant	7 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



MSL 1
Pb Free
260°C



AEC-Q200
based qualification

Dimensions WWWW

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
1206	3.2 ± 0.4	1.6 ± 0.25	1.5 max	0.2 min
	(0.126 ± 0.016)	(0.063 ± 0.01)	(0.059) max	(0.008) min



How to Order (Packaging options)

NB	20	Q0	0334	K	BC
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NB = Ni/Sn Term for lead free soldering	20 = 1206	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BA = Plastic tape (180mm reel, 3,000 pcs/reel) BE = Plastic tape (180mm reel, 1,500 pcs/reel) BC = Plastic tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)
				* For selected PNs	

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

Material Table

Q0 (B25/85 = 4300K $\pm 3\%$)

T (°C)	R(T) / R25	TF (%)	α (%/°C)
-55	98.04	25.30	-6.87
-50	69.53	21.86	-6.70
-45	49.73	18.79	-6.53
-40	35.87	16.07	-6.37
-35	26.08	13.65	-6.22
-30	19.12	11.50	-6.07
-25	14.12	9.60	-5.92
-20	10.51	7.93	-5.78
-15	7.877	6.45	-5.64
-10	5.947	5.16	-5.50
-5	4.521	4.04	-5.37
0	3.460	3.06	-5.24
5	2.666	2.22	-5.11
10	2.067	1.51	-4.99
15	1.613	0.91	-4.87
20	1.266	0.41	-4.75
25	1.000	0.00	-4.63
30	0.7944	0.39	-4.52
35	0.6347	0.84	-4.41
40	0.5099	1.33	-4.30
45	0.4119	1.87	-4.20
50	0.3344	2.45	-4.09
55	0.2730	3.06	-3.99
60	0.2239	3.70	-3.90
65	0.1846	4.37	-3.80
70	0.1529	5.06	-3.71
75	0.1272	5.77	-3.62
80	0.1063	6.50	-3.53
85	0.0893	7.25	-3.44
90	0.0753	8.01	-3.36
95	0.0637	8.78	-3.28
100	0.0542	9.57	-3.20
105	0.0462	10.36	-3.13
110	0.0396	11.15	-3.05
115	0.0340	11.96	-2.98
120	0.0294	12.77	-2.91
125	0.0254	13.58	-2.84
130	0.0221	14.39	-2.77
135	0.0193	15.21	-2.71
140	0.0169	16.03	-2.64
145	0.0148	16.84	-2.58
150	0.0130	17.66	-2.52

B25/50	B25/75	B25/85	B25/100	B Tol
4221 K	4281 K	4300 K	4325 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
20,933,030	32,354,199	43,775,368
15,634,092	22,943,579	30,253,067
11,685,731	16,411,166	21,136,600
8,751,515	11,837,306	14,923,096
6,572,343	8,607,883	10,643,422
4,952,634	6,309,156	7,665,678
3,746,548	4,659,988	5,573,427
2,846,123	3,467,758	4,089,394
2,171,765	2,599,439	3,027,113
1,664,903	1,962,445	2,259,986
1,282,445	1,491,851	1,701,256
992,659	1,141,798	1,290,937
772,143	879,666	987,189
603,592	682,089	760,587
474,176	532,221	590,267
374,353	417,835	461,317
297,000	330,000	363,000
234,911	262,154	289,397
186,746	209,446	232,145
149,197	168,266	187,335
119,783	135,916	152,050
96,630	110,367	124,104
78,320	90,082	101,844
63,773	73,895	84,017
52,162	60,913	69,664
42,855	50,452	58,048
35,360	41,980	48,601
29,299	35,089	40,880
24,377	29,459	34,540
20,364	24,837	29,310
17,078	21,028	24,977
14,378	17,875	21,372
12,149	15,254	18,359
10,303	13,068	15,832
8,768.8	11,236	13,704
7,488.7	9,696.3	11,904
6,416.9	8,396.9	10,377
5,516.5	7,296.4	9,076.3
4,757.5	6,361.1	7,964.8
4,115.6	5,563.6	7,011.6
3,571.0	4,881.3	6,191.6
3,107.5	4,295.7	5,483.9