


## NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

**SpiCAT**



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

## Characteristics

Case Size	0603
Operating temperature	-55°C to +150°C
Resistance	68 kOhm
Tolerance on Resistance (25°C)	$\pm 3\%$
B 25/85	4080K $\pm 3\%$
Maximum dissipation at 25°C	0.07 W
Thermal dissipation factor	1 mW/°C
Thermal time constant	4 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



MSL 1  
Pb Free  
260°C



AEC-Q200  
based qualification

## Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
0603	1.6 $\pm 0.2$	0.8 $\pm 0.2$	1.0 max	0.2 min
	(0.063 $\pm 0.008$ )	(0.031 $\pm 0.008$ )	(0.039) max	(0.008) min



## How to Order (Packaging options)

<b>NB</b>	<b>21</b>	<b>N0</b>	<b>0683</b>	<b>H</b>	<b>BF</b>
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NB = Ni/Sn Term for lead free soldering	21 = 0603	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BB = Cardboard tape (180mm reel, 4,000 pcs/reel) BF = Cardboard tape (180mm reel, 2,000 pcs/reel) BD = Cardboard tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)

\* For selected PNs

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

## Material Table

**N0 (B25/85 = 4080K $\pm 3\%$ )**

T (°C)	R(T) / R25	TF (%)	$\alpha$ (%/°C)
-55	110.1	24.01	-7.50
-50	75.89	20.74	-7.25
-45	52.97	17.83	-7.01
-40	37.42	15.25	-6.78
-35	26.75	12.95	-6.56
-30	19.33	10.91	-6.35
-25	14.11	9.11	-6.14
-20	10.41	7.52	-5.95
-15	7.758	6.12	-5.76
-10	5.834	4.90	-5.58
-5	4.426	3.83	-5.41
0	3.387	2.91	-5.24
5	2.614	2.11	-5.08
10	2.033	1.43	-4.93
15	1.593	0.86	-4.78
20	1.258	0.39	-4.64
25	1.000	0.00	-4.51
30	0.8004	0.37	-4.37
35	0.6449	0.80	-4.25
40	0.5228	1.26	-4.13
45	0.4264	1.77	-4.01
50	0.3497	2.32	-3.90
55	0.2885	2.90	-3.79
60	0.2392	3.51	-3.68
65	0.1994	4.14	-3.58
70	0.1671	4.80	-3.49
75	0.1406	5.48	-3.39
80	0.1189	6.17	-3.30
85	0.1010	6.88	-3.22
90	0.0862	7.60	-3.13
95	0.0738	8.33	-3.05
100	0.0635	9.08	-2.97
105	0.0548	9.83	-2.90
110	0.0475	10.58	-2.83
115	0.0413	11.35	-2.76
120	0.0360	12.11	-2.69
125	0.0315	12.89	-2.62
130	0.0277	13.66	-2.56
135	0.0244	14.43	-2.50
140	0.0216	15.21	-2.44
145	0.0191	15.98	-2.38
150	0.0170	16.76	-2.33

B25/50	B25/75	B25/85	B25/100	B Tol
4049 K	4072 K	4080 K	4090 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
5,464,741	7,486,619	9,508,497
3,935,344	5,160,477	6,385,609
2,851,700	3,602,127	4,352,554
2,080,488	2,544,834	3,009,180
1,528,657	1,818,736	2,108,814
1,131,405	1,314,253	1,497,101
843,574	959,815	1,076,055
633,617	708,117	782,616
479,409	527,533	575,658
365,359	396,689	428,019
280,425	300,983	321,541
216,737	230,339	243,941
168,656	177,737	186,818
132,113	138,239	144,365
104,158	108,340	112,522
82,635	85,531	88,427
65,960	68,000	70,040
52,593	54,429	56,264
42,186	43,850	45,514
34,032	35,548	37,064
27,608	28,992	30,376
22,517	23,782	25,048
18,460	19,617	20,775
15,209	16,268	17,327
12,592	13,561	14,530
10,474	11,360	12,246
8,752	9,563	10,373
7,345	8,086	8,828
6,190	6,869	7,547
5,238	5,859	6,480
4,450	5,019	5,588
3,795	4,316	4,837
3,248	3,726	4,204
2,790	3,229	3,667
2,405	2,808	3,211
2,080	2,450	2,820
1,804	2,145	2,486
1,570	1,884	2,198
1,371	1,660	1,950
1,200	1,467	1,734
1,054	1,301	1,547
927.6	1,156	1,384