
NC12J00562MBD

(0805, 5600 Ohm ±20%, 3480K, AgPdPt)

NTC SMD Thermistor with AgPdPt termination

for Automotive, Industrial and General applications

To view data online visit:
SpiCAT



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. AgPdPt termination termination for conductive adhesive assembly (not suitable for lead free soldering - use NB series).

Characteristics

Case Size	0805
Operating temperature	-55°C to +150°C
Resistance	5600 Ohm
Tolerance on Resistance (25°C)	±20%
B 25/85	3480K±3%
Maximum dissipation at 25°C	0.12 W
Thermal dissipation factor	2 mW/°C
Thermal time constant	5 s
Termination	AgPdPt (for conductive adhesive)

RoHS COMPLIANT


MSL 1

AEC-Q200 based qualification

Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
0805	2.0±0.3	1.25±0.2	1.3 max	0.2 min
	(0.079±0.012)	(0.049±0.008)	(0.051) max	(0.008) min



How to Order (Packaging options)

NC	12	J0	0562	M	BD
Type	**Size**	**Material Code**	**Resistance (Ohm)**	**Tolerance**	**Suffix: Packaging**
NC = AgPdPt for conductive adhesive	12 = 0805	See Datasheet	2 Sig. Digits + Number of Zeros	H = ±3%* J = ±5% K = ±10% M = ±20%	BB = Cardboard tape (180mm reel, 4,000 pcs/reel) BF = Cardboard tape (180mm reel, 2,000 pcs/reel) BD = Cardboard tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)

* For selected PNs

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are beleived to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

Material Table

J0 (B25/85 = 3480K±3%)

B25/50	B25/75	B25/85	B25/100	B Tol
3443 K	3471 K	3480 K	3492 K	±3%

T (°C)	R(T) / R25	TF (%)	α (%/°C)	R Min (Ω)	R Nom (Ω)	R Max (Ω)
-55	51.75	20.47	-6.23	172,507	289,807	407,106
-50	37.98	17.69	-6.03	132,521	212,678	292,836
-45	28.15	15.21	-5.84	102,142	157,649	213,157
-40	21.07	13.00	-5.65	79,047	117,987	156,927
-35	15.91	11.04	-5.48	61,454	89,121	116,789
-30	12.13	9.31	-5.31	48,011	67,916	87,820
-25	9.321	7.77	-5.15	37,702	52,197	66,692
-20	7.222	6.41	-4.99	29,762	40,445	51,128
-15	5.640	5.22	-4.84	23,619	31,585	39,552
-10	4.438	4.18	-4.69	18,844	24,853	30,861
-5	3.517	3.27	-4.55	15,114	19,697	24,280
0	2.807	2.48	-4.42	12,187	15,720	19,254
5	2.255	1.80	-4.29	9,877.1	12,630	15,384
10	1.824	1.22	-4.17	8,046.1	10,213	12,381
15	1.484	0.73	-4.05	6,587.3	8,310.4	10,033
20	1.215	0.33	-3.93	5,419.5	6,802.3	8,185.2
25	1.000	0.00	-3.82	4,480.0	5,600.0	6,720.0
30	0.8278	0.32	-3.71	3,693.9	4,635.7	5,577.6
35	0.6889	0.68	-3.61	3,060.2	3,858.0	4,655.8
40	0.5763	1.08	-3.51	2,547.0	3,227.3	3,907.5
45	0.4845	1.51	-3.41	2,129.4	2,713.0	3,296.7
50	0.4092	1.98	-3.32	1,787.9	2,291.6	2,795.3
55	0.3472	2.47	-3.23	1,507.6	1,944.6	2,381.6
60	0.2960	2.99	-3.15	1,276.3	1,657.4	2,038.5
65	0.2533	3.53	-3.06	1,084.8	1,418.7	1,752.6
70	0.2177	4.09	-2.98	925.6	1,219.4	1,513.2
75	0.1879	4.67	-2.90	792.7	1,052.3	1,311.8
80	0.1628	5.26	-2.83	681.3	911.5	1,141.8
85	0.1415	5.87	-2.76	587.5	792.5	997.5
90	0.1235	6.48	-2.69	508.4	691.5	874.7
95	0.1081	7.11	-2.62	441.4	605.5	769.6
100	0.0950	7.74	-2.55	384.4	532.0	679.5
105	0.0837	8.38	-2.49	335.8	468.8	601.9
110	0.0740	9.03	-2.43	294.2	414.5	534.8
115	0.0656	9.68	-2.37	258.5	367.6	476.7
120	0.0584	10.33	-2.31	227.7	326.9	426.1
125	0.0521	10.99	-2.26	201.2	291.5	381.9
130	0.0466	11.65	-2.21	178.2	260.7	343.2
135	0.0417	12.31	-2.15	158.2	233.8	309.3
140	0.0375	12.97	-2.10	140.9	210.2	279.4
145	0.0338	13.63	-2.06	125.7	189.4	253.1
150	0.0305	14.29	-2.01	112.4	171.1	229.7