


## NTC SMD Thermistor with AgPdPt termination

for Automotive, Industrial and General applications

To view data online visit:

**SpiCAT**



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. AgPdPt termination termination for conductive adhesive assembly (not suitable for lead free soldering - use NB series).

## Characteristics

Case Size	0805
Operating temperature	-55°C to +150°C
Resistance	1000 Ohm
Tolerance on Resistance (25°C)	$\pm 10\%$
B 25/85	3910K $\pm 3\%$
Maximum dissipation at 25°C	0.12 W
Thermal dissipation factor	2 mW/°C
Thermal time constant	5 s
Termination	AgPdPt (for conductive adhesive)



MSL 1




**AEC-Q200**  
based qualification

## Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
0805	2.0 $\pm 0.3$	1.25 $\pm 0.2$	1.3 max	0.2 min
	(0.079 $\pm 0.012$ )	(0.049 $\pm 0.008$ )	(0.051) max	(0.008) min



## How to Order (Packaging options)

<b>NC</b>	<b>12</b>	<b>MC</b>	<b>0102</b>	<b>K</b>	<b>--</b>
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NC = AgPdPt for conductive adhesive	12 = 0805	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BB = Cardboard tape (180mm reel, 4,000 pcs/reel) BF = Cardboard tape (180mm reel, 2,000 pcs/reel) BD = Cardboard tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)

\* For selected PNs

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

## Material Table

MC (B25/85 = 3910K $\pm 3\%$ )

T (°C)	R(T) / R25	TF (%)	$\alpha$ (%/°C)
-55	100.6	23.00	-7.56
-50	69.29	19.90	-7.27
-45	48.40	17.10	-7.00
-40	34.27	14.60	-6.75
-35	24.57	12.40	-6.50
-30	17.83	10.50	-6.27
-25	13.09	8.70	-6.05
-20	9.710	7.20	-5.84
-15	7.282	5.90	-5.64
-10	5.514	4.70	-5.45
-5	4.215	3.70	-5.27
0	3.250	2.80	-5.10
5	2.528	2.00	-4.93
10	1.982	1.40	-4.77
15	1.567	0.80	-4.62
20	1.247	0.40	-4.48
25	1.000	0.00	-4.34
30	0.8072	0.40	-4.21
35	0.6559	0.80	-4.08
40	0.5362	1.20	-3.96
45	0.4410	1.70	-3.85
50	0.3647	2.20	-3.74
55	0.3033	2.80	-3.63
60	0.2535	3.40	-3.53
65	0.2130	4.00	-3.43
70	0.1798	4.60	-3.34
75	0.1525	5.20	-3.25
80	0.1300	5.90	-3.16
85	0.1112	6.60	-3.08
90	0.0955	7.30	-2.99
95	0.0824	8.00	-2.92
100	0.0713	8.70	-2.84
105	0.0620	9.40	-2.77
110	0.0541	10.10	-2.70
115	0.0473	10.90	-2.63
120	0.0415	11.60	-2.57
125	0.0366	12.30	-2.51
130	0.0323	13.10	-2.45
135	0.0286	13.80	-2.39
140	0.0254	14.60	-2.33
145	0.0227	15.30	-2.28
150	0.0203	16.10	-2.23

B25/50	B25/75	B25/85	B25/100	B Tol
3887 K	3904 K	3910 K	3917 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
67,402	100,600	133,798
48,572	69,290	90,008
35,284	48,400	61,516
25,840	34,270	42,700
19,066	24,570	30,074
14,175	17,830	21,485
10,642	13,090	15,538
8,039.9	9,710.0	11,380
6,124.2	7,282.0	8,439.8
4,703.4	5,514.0	6,324.6
3,637.5	4,215.0	4,792.5
2,834.0	3,250.0	3,666.0
2,224.6	2,528.0	2,831.4
1,756.1	1,982.0	2,207.9
1,397.8	1,567.0	1,736.2
1,117.3	1,247.0	1,376.7
900.0	1,000.0	1,100.0
723.3	807.2	891.1
585.1	655.9	726.7
476.1	536.2	596.3
389.4	441.0	492.6
320.2	364.7	409.2
264.5	303.3	342.1
219.5	253.5	287.5
183.2	213.0	242.8
153.5	179.8	206.1
129.3	152.5	175.7
109.3	130.0	150.7
92.7	111.2	129.7
79.0	95.5	112.0
67.6	82.4	97.2
58.0	71.3	84.7
50.0	62.0	74.0
43.2	54.1	64.9
37.4	47.3	57.2
32.6	41.5	50.5
28.4	36.6	44.7
24.8	32.3	39.8
21.8	28.6	35.4
19.2	25.4	31.7
16.9	22.7	28.4
15.0	20.3	25.5