


NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

SpiCAT



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

Characteristics

Case Size	0603
Operating temperature	-55°C to +150°C
Resistance	5000 Ohm
Tolerance on Resistance (25°C)	$\pm 3\%$
B 25/85	3480K $\pm 3\%$
Maximum dissipation at 25°C	0.07 W
Thermal dissipation factor	1 mW/°C
Thermal time constant	4 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



RoHS
COMPLIANT

MSL 1
Pb Free
260°C



AEC-Q200
based qualification

Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
0603	1.6 ± 0.2	0.8 ± 0.2	1.0 max	0.2 min
	(0.063 ± 0.008)	(0.031 ± 0.008)	(0.039) max	(0.008) min



How to Order (Packaging options)

NB

Type

NB = Ni/Sn Term for lead free soldering

21

Size

21 = 0603

J0

Material Code

See Datasheet

0502

Resistance (Ohm)

2 Sig. Digits + Number of Zeros

H

Tolerance

H = $\pm 3\%$ *
J = $\pm 5\%$
K = $\pm 10\%$
M = $\pm 20\%$

* For selected PNs

BF

Suffix: Packaging

BB = Cardboard tape (180mm reel, 4,000 pcs/reel)
BF = Cardboard tape (180mm reel, 2,000 pcs/reel)
BD = Cardboard tape (330mm reel, 10,000 pcs/reel)
-- = Bulk (5000 pcs/bag)

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

Material Table

J0 (B25/85 = 3480K $\pm 3\%$)

T (°C)	R(T) / R25	TF (%)	α (%/°C)
-55	51.75	20.47	-6.23
-50	37.98	17.69	-6.03
-45	28.15	15.21	-5.84
-40	21.07	13.00	-5.65
-35	15.91	11.04	-5.48
-30	12.13	9.31	-5.31
-25	9.321	7.77	-5.15
-20	7.222	6.41	-4.99
-15	5.640	5.22	-4.84
-10	4.438	4.18	-4.69
-5	3.517	3.27	-4.55
0	2.807	2.48	-4.42
5	2.255	1.80	-4.29
10	1.824	1.22	-4.17
15	1.484	0.73	-4.05
20	1.215	0.33	-3.93
25	1.000	0.00	-3.82
30	0.8278	0.32	-3.71
35	0.6889	0.68	-3.61
40	0.5763	1.08	-3.51
45	0.4845	1.51	-3.41
50	0.4092	1.98	-3.32
55	0.3472	2.47	-3.23
60	0.2960	2.99	-3.15
65	0.2533	3.53	-3.06
70	0.2177	4.09	-2.98
75	0.1879	4.67	-2.90
80	0.1628	5.26	-2.83
85	0.1415	5.87	-2.76
90	0.1235	6.48	-2.69
95	0.1081	7.11	-2.62
100	0.0950	7.74	-2.55
105	0.0837	8.38	-2.49
110	0.0740	9.03	-2.43
115	0.0656	9.68	-2.37
120	0.0584	10.33	-2.31
125	0.0521	10.99	-2.26
130	0.0466	11.65	-2.21
135	0.0417	12.31	-2.15
140	0.0375	12.97	-2.10
145	0.0338	13.63	-2.06
150	0.0305	14.29	-2.01

B25/50	B25/75	B25/85	B25/100	B Tol
3443 K	3471 K	3480 K	3492 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
198,013	258,756	319,499
150,604	189,891	229,179
115,127	140,758	166,390
88,487	105,346	122,205
68,397	79,573	90,748
53,176	60,639	68,102
41,585	46,604	51,624
32,712	36,111	39,511
25,882	28,201	30,520
20,597	22,190	23,782
16,485	17,587	18,689
13,267	14,036	14,805
10,736	11,277	11,818
8,734	9,119	9,504
7,143	7,420	7,697
5,871	6,074	6,276
4,850	5,000	5,150
4,002	4,139	4,276
3,318	3,445	3,571
2,764	2,881	2,999
2,313	2,422	2,532
1,944	2,046	2,148
1,641	1,736	1,831
1,391	1,480	1,569
1,184	1,267	1,349
1,012	1,089	1,166
867.5	939.5	1,012
746.6	813.9	881.1
644.9	707.6	770.4
558.9	617.4	676.0
486.0	540.6	595.3
423.9	475.0	526.0
371.0	418.6	466.3
325.6	370.1	414.6
286.6	328.2	369.8
253.0	291.9	330.8
223.9	260.3	296.7
198.7	232.8	266.9
176.8	208.7	240.7
157.7	187.6	217.6
141.0	169.1	197.2
126.3	152.7	179.2