


NTC SMD Thermistor with Ni/Sn termination

for Automotive, Industrial and General applications

To view data online visit:

SpiCAT



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. Ni barrier/100% Sn plated termination for lead free soldering.

Characteristics

Case Size	0603
Operating temperature	-55°C to +150°C
Resistance	10 kOhm
Tolerance on Resistance (25°C)	$\pm 5\%$
B 25/85	3480K $\pm 3\%$
Maximum dissipation at 25°C	0.07 W
Thermal dissipation factor	1 mW/°C
Thermal time constant	4 s
Termination	Ni barrier/100%Sn (for Pb free soldering)



MSL 1
Pb Free
260°C



AEC-Q200
based qualification

Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
0603	1.6 ± 0.2	0.8 ± 0.2	1.0 max	0.2 min
	(0.063 ± 0.008)	(0.031 ± 0.008)	(0.039) max	(0.008) min



How to Order (Packaging options)

NB	21	J5	0103	J	BF
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NB = Ni/Sn Term for lead free soldering	21 = 0603	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BB = Cardboard tape (180mm reel, 4,000 pcs/reel) BF = Cardboard tape (180mm reel, 2,000 pcs/reel) BD = Cardboard tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)

* For selected PNs

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

Material Table

J5 (B25/85 = 3480K $\pm 3\%$)

T (°C)	R(T) / R25	TF (%)	α (%/°C)
-55	51.75	20.47	-6.23
-50	37.98	17.69	-6.03
-45	28.15	15.21	-5.84
-40	21.07	13.00	-5.65
-35	15.91	11.04	-5.48
-30	12.13	9.31	-5.31
-25	9.321	7.77	-5.15
-20	7.222	6.41	-4.99
-15	5.640	5.22	-4.84
-10	4.438	4.18	-4.69
-5	3.517	3.27	-4.55
0	2.807	2.48	-4.42
5	2.255	1.80	-4.29
10	1.824	1.22	-4.17
15	1.484	0.73	-4.05
20	1.215	0.33	-3.93
25	1.000	0.00	-3.82
30	0.8278	0.32	-3.71
35	0.6889	0.68	-3.61
40	0.5763	1.08	-3.51
45	0.4845	1.51	-3.41
50	0.4092	1.98	-3.32
55	0.3472	2.47	-3.23
60	0.2960	2.99	-3.15
65	0.2533	3.53	-3.06
70	0.2177	4.09	-2.98
75	0.1879	4.67	-2.90
80	0.1628	5.26	-2.83
85	0.1415	5.87	-2.76
90	0.1235	6.48	-2.69
95	0.1081	7.11	-2.62
100	0.0950	7.74	-2.55
105	0.0837	8.38	-2.49
110	0.0740	9.03	-2.43
115	0.0656	9.68	-2.37
120	0.0584	10.33	-2.31
125	0.0521	10.99	-2.26
130	0.0466	11.65	-2.21
135	0.0417	12.31	-2.15
140	0.0375	12.97	-2.10
145	0.0338	13.63	-2.06
150	0.0305	14.29	-2.01

B25/50	B25/75	B25/85	B25/100	B Tol
3443 K	3471 K	3480 K	3492 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
385,676	517,512	649,348
293,612	379,782	465,953
224,623	281,517	338,410
172,759	210,691	248,624
133,611	159,145	184,679
103,926	121,278	138,630
81,306	93,209	105,112
63,979	72,223	80,467
50,637	56,402	62,167
40,307	44,380	48,452
32,266	35,173	38,081
25,973	28,072	30,171
21,021	22,554	24,088
17,104	18,238	19,373
13,989	14,840	15,691
11,500	12,147	12,794
9,500	10,000	10,500
7,838	8,278	8,718
6,498	6,889	7,280
5,413	5,763	6,113
4,529	4,845	5,160
3,807	4,092	4,378
3,213	3,472	3,732
2,723	2,960	3,196
2,317	2,533	2,750
1,979	2,177	2,375
1,697	1,879	2,061
1,461	1,628	1,795
1,261	1,415	1,569
1,093	1,235	1,377
950.4	1,081	1,212
828.9	949.9	1,071
725.2	837.2	949.2
636.4	740.2	844.0
560.0	656.4	752.7
494.2	583.7	673.3
437.4	520.6	603.9
388.1	465.6	543.1
345.2	417.5	489.7
307.8	375.3	442.7
275.2	338.2	401.2
246.6	305.5	364.4