


## NTC SMD Thermistor with AgPdPt termination

for Automotive, Industrial and General applications

To view data online visit:

**SpiCAT**



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. AgPdPt termination termination for conductive adhesive assembly (not suitable for lead free soldering - use NB series).

## Characteristics

Case Size	1206
Operating temperature	-55°C to +150°C
Resistance	1500 Ohm
Tolerance on Resistance (25°C)	$\pm 10\%$
B 25/85	3910K $\pm 3\%$
Maximum dissipation at 25°C	0.24 W
Thermal dissipation factor	4 mW/°C
Thermal time constant	7 s
Termination	AgPdPt (for conductive adhesive)



MSL 1




**AEC-Q200**  
based qualification

## Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
1206	3.2 $\pm 0.4$	1.6 $\pm 0.25$	1.5 max	0.2 min
	(0.126 $\pm 0.016$ )	(0.063 $\pm 0.01$ )	(0.059) max	(0.008) min



## How to Order (Packaging options)

<b>NC</b>	<b>20</b>	<b>MC</b>	<b>0152</b>	<b>K</b>	<b>BA</b>
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NC = AgPdPt for conductive adhesive	20 = 1206	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BA = Plastic tape (180mm reel, 3,000 pcs/reel) BE = Plastic tape (180mm reel, 1,500 pcs/reel) BC = Plastic tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)
				* For selected PNs	

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

## Material Table

MC (B25/85 = 3910K $\pm 3\%$ )

T (°C)	R(T) / R25	TF (%)	$\alpha$ (%/°C)
-55	100.6	23.00	-7.56
-50	69.29	19.90	-7.27
-45	48.40	17.10	-7.00
-40	34.27	14.60	-6.75
-35	24.57	12.40	-6.50
-30	17.83	10.50	-6.27
-25	13.09	8.70	-6.05
-20	9.710	7.20	-5.84
-15	7.282	5.90	-5.64
-10	5.514	4.70	-5.45
-5	4.215	3.70	-5.27
0	3.250	2.80	-5.10
5	2.528	2.00	-4.93
10	1.982	1.40	-4.77
15	1.567	0.80	-4.62
20	1.247	0.40	-4.48
25	1.000	0.00	-4.34
30	0.8072	0.40	-4.21
35	0.6559	0.80	-4.08
40	0.5362	1.20	-3.96
45	0.4410	1.70	-3.85
50	0.3647	2.20	-3.74
55	0.3033	2.80	-3.63
60	0.2535	3.40	-3.53
65	0.2130	4.00	-3.43
70	0.1798	4.60	-3.34
75	0.1525	5.20	-3.25
80	0.1300	5.90	-3.16
85	0.1112	6.60	-3.08
90	0.0955	7.30	-2.99
95	0.0824	8.00	-2.92
100	0.0713	8.70	-2.84
105	0.0620	9.40	-2.77
110	0.0541	10.10	-2.70
115	0.0473	10.90	-2.63
120	0.0415	11.60	-2.57
125	0.0366	12.30	-2.51
130	0.0323	13.10	-2.45
135	0.0286	13.80	-2.39
140	0.0254	14.60	-2.33
145	0.0227	15.30	-2.28
150	0.0203	16.10	-2.23

B25/50	B25/75	B25/85	B25/100	B Tol
3887 K	3904 K	3910 K	3917 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
101,103	150,900	200,697
72,858	103,935	135,012
52,925	72,600	92,275
38,759	51,405	64,051
28,599	36,855	45,111
21,262	26,745	32,228
15,963	19,635	23,307
12,060	14,565	17,070
9,186.2	10,923	12,660
7,055.2	8,271.0	9,486.8
5,456.3	6,322.5	7,188.7
4,251.0	4,875.0	5,499.0
3,337.0	3,792.0	4,247.0
2,634.1	2,973.0	3,311.9
2,096.6	2,350.5	2,604.4
1,676.0	1,870.5	2,065.0
1,350.0	1,500.0	1,650.0
1,084.9	1,210.8	1,336.7
877.6	983.9	1,090.1
714.2	804.3	894.4
584.1	661.5	738.9
480.3	547.1	613.8
396.7	455.0	513.2
329.3	380.3	431.2
274.8	319.5	364.2
230.3	269.7	309.1
194.0	228.8	263.5
164.0	195.0	226.0
139.1	166.8	194.5
118.5	143.3	168.1
101.3	123.6	145.8
87.0	107.0	127.0
74.9	93.0	111.0
64.8	81.1	97.4
56.1	71.0	85.8
48.8	62.3	75.8
42.6	54.9	67.1
37.3	48.5	59.7
32.7	42.9	53.2
28.8	38.2	47.5
25.4	34.0	42.6
22.4	30.4	38.3