


## NTC SMD Thermistor with AgPdPt termination

for Automotive, Industrial and General applications

To view data online visit:

**SpiCAT**



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. AgPdPt termination termination for conductive adhesive assembly (not suitable for lead free soldering - use NB series).

## Characteristics

Case Size	0603
Operating temperature	-55°C to +150°C
Resistance	68 kOhm
Tolerance on Resistance (25°C)	$\pm 10\%$
B 25/85	4080K $\pm 3\%$
Maximum dissipation at 25°C	0.07 W
Thermal dissipation factor	1 mW/°C
Thermal time constant	4 s
Termination	AgPdPt (for conductive adhesive)



MSL 1



**AEC-Q200**  
based qualification

## Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
0603	1.6 $\pm 0.2$	0.8 $\pm 0.2$	1.0 max	0.2 min
	(0.063 $\pm 0.008$ )	(0.031 $\pm 0.008$ )	(0.039) max	(0.008) min



## How to Order (Packaging options)

**NC**

Type

NC = AgPdPt for conductive adhesive

**21**

Size

21 = 0603

**N0**

Material Code

See Datasheet

**0683**

Resistance (Ohm)

2 Sig. Digits + Number of Zeros

**K**

Tolerance

H =  $\pm 3\%$ \*  
J =  $\pm 5\%$   
K =  $\pm 10\%$   
M =  $\pm 20\%$

\* For selected PNs

**--**

Suffix: Packaging

BB = Cardboard tape (180mm reel, 4,000 pcs/reel)  
BF = Cardboard tape (180mm reel, 2,000 pcs/reel)  
BD = Cardboard tape (330mm reel, 10,000 pcs/reel)  
-- = Bulk (5000 pcs/bag)

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

## Material Table

**N0 (B25/85 = 4080K $\pm 3\%$ )**

T (°C)	R(T) / R25	TF (%)	$\alpha$ (%/°C)
-55	110.1	24.01	-7.50
-50	75.89	20.74	-7.25
-45	52.97	17.83	-7.01
-40	37.42	15.25	-6.78
-35	26.75	12.95	-6.56
-30	19.33	10.91	-6.35
-25	14.11	9.11	-6.14
-20	10.41	7.52	-5.95
-15	7.758	6.12	-5.76
-10	5.834	4.90	-5.58
-5	4.426	3.83	-5.41
0	3.387	2.91	-5.24
5	2.614	2.11	-5.08
10	2.033	1.43	-4.93
15	1.593	0.86	-4.78
20	1.258	0.39	-4.64
25	1.000	0.00	-4.51
30	0.8004	0.37	-4.37
35	0.6449	0.80	-4.25
40	0.5228	1.26	-4.13
45	0.4264	1.77	-4.01
50	0.3497	2.32	-3.90
55	0.2885	2.90	-3.79
60	0.2392	3.51	-3.68
65	0.1994	4.14	-3.58
70	0.1671	4.80	-3.49
75	0.1406	5.48	-3.39
80	0.1189	6.17	-3.30
85	0.1010	6.88	-3.22
90	0.0862	7.60	-3.13
95	0.0738	8.33	-3.05
100	0.0635	9.08	-2.97
105	0.0548	9.83	-2.90
110	0.0475	10.58	-2.83
115	0.0413	11.35	-2.76
120	0.0360	12.11	-2.69
125	0.0315	12.89	-2.62
130	0.0277	13.66	-2.56
135	0.0244	14.43	-2.50
140	0.0216	15.21	-2.44
145	0.0191	15.98	-2.38
150	0.0170	16.76	-2.33

B25/50	B25/75	B25/85	B25/100	B Tol
4049 K	4072 K	4080 K	4090 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
4,940,678	7,486,619	10,032,560
3,574,111	5,160,477	6,746,843
2,599,551	3,602,127	4,604,703
1,902,350	2,544,834	3,187,319
1,401,346	1,818,736	2,236,126
1,039,407	1,314,253	1,589,098
776,387	959,815	1,143,242
584,049	708,117	832,184
442,481	527,533	612,585
337,591	396,689	455,787
259,356	300,983	342,609
200,613	230,339	260,065
156,214	177,737	199,260
122,436	138,239	154,041
96,574	108,340	120,106
76,648	85,531	94,414
61,200	68,000	74,800
48,783	54,429	60,074
39,116	43,850	48,584
31,544	35,548	39,553
25,578	28,992	32,406
20,852	23,782	26,712
17,086	19,617	22,148
14,071	16,268	18,466
11,643	13,561	15,479
9,679	11,360	13,042
8,083	9,563	11,042
6,779	8,086	9,394
5,709	6,869	8,028
4,828	5,859	6,890
4,099	5,019	5,939
3,493	4,316	5,139
2,987	3,726	4,465
2,564	3,229	3,893
2,208	2,808	3,407
1,908	2,450	2,992
1,654	2,145	2,636
1,438	1,884	2,330
1,255	1,660	2,066
1,097	1,467	1,837
962.6	1,301	1,638
846.7	1,156	1,465