


F38 Series ----- F380J107MSALZT

Conductive Polymer, Miniature, Undertab Solid Electrolytic Chip Capacitors



PRODUCT SPECIFICATIONS :

Nominal Capacitance @ 120Hz	100 μ F
Capacitance Tolerance	M = \pm 20%
Rated Voltage DC (V_R)	< 60°C 6.3 V
Category Voltage DC (V_C)	< 105°C 3.3 V
Surge Voltage (V_S)	< 60°C 8 V
Temperature Range	-55°C to +105°C
DC Leakage Current max. @ V_R	126 μ A
Dissipation Factor max. @ 120Hz	10 %
ESR max. @ 100kHz	200 m Ω
Typical weight (S case)	12.4 mg
Moisture sensitivity level:	MSL 3
Reflow specification: meets J-STD-020 standard	
100% surge current tested	
All technical data relates to an ambient temperature of +20°C, Capacitance is measured at 120Hz, 0.5RMS with DC bias of 1.5V, DC Leakage Current is measured at rated voltage after 5 minutes	




LEAD-FREE
LEAD-FREE COMPATIBLE
COMPONENT



RMS value of Ripple Current (mA) @100kHz			
45°C	60°C	85°C	105°C
474	332	—	237


HOW TO ORDER :



Special Code

AXE	Rated temp. 60°C, H dimension 1.0mm Max
AXEH3	Rated temp. 60°C, H dimension 1.0mm Max, Low ESR
LZT	Rated temp. 60°C
LZTH1	Rated temp. 60°C, Low ESR
AH1, AH2, AH3	Low ESR
H8Z	H dimension 0.8mm Max

MARKING :




RV	*	Cap	**
4	G	1	A
6.3	J	2.2	J
8	K	4.7	S
10	A	10	a
25	E	22	J
30	S	33	n
		47	s
		68	w
		100	A

F38 Series ----- F380J107MSALZT
Conductive Polymer, Miniature, Undertab Solid Electrolytic Chip Capacitors



CASE DIMENSIONS: millimetres

Case Code	EIA Code	EIA Metric	L	W ₁	W ₂	H	S ₁	S ₂
S	0805	2012-09	2.0 +0.2/-0.1	1.25 +0.2/-0.1	0.9±0.1	0.8±0.1	0.5±0.1	1.0±0.1



PACKAGING INFORMATION :

Packaging Code	Reel Size	Tape Width	Quantity (pcs)
A	180 mm	8 mm	4,000

Issued by: KYOCERA AVX Technical Marketing Team
Tantalum Division
More details at: www.kyocera-avx.com

Version: 10/2021

NORTH AMERICA
Tel: +1 864-967-2150

CENTRAL AMERICA
Tel: +55 11-46881960

EUROPE
Tel: +44 1276-697000

ASIA
Tel: +65 6286-7555

JAPAN
Tel: +81 740-321250

WWW.KYOCERA-AVX.COM



NOTICE: Specifications are subject to change without notice. Contact your nearest KYOCERA AVX Sales Office for the latest specifications. Specifications are typical and may not apply to all applications. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements or suggestions concerning possible use of our product are made without responsibility or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should not assume that all safety measures are indicated or that other measures are indicated or that measures may not be required. All samples are provided for testing purposes only. Provision of samples shall not constitute any offer of sale nor shall it constitute any commitment of any kind. Samples may not be incorporated in any product offered for commercial sale. Recipient assumes all risks and liability resulting from such testing. Samples are for the exclusive use of the direct recipient and shall not be sold, lent, given, or otherwise transferred to any other party. All unused samples shall be destroyed or returned to KYOCERA AVX.