


NTC SMD Thermistor with AgPdPt termination

for Automotive, Industrial and General applications

To view data online visit:

SpiCAT



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. AgPdPt termination termination for conductive adhesive assembly (not suitable for lead free soldering - use NB series).

Characteristics

Case Size	0805
Operating temperature	-55°C to +150°C
Resistance	56 kOhm
Tolerance on Resistance (25°C)	$\pm 5\%$
B 25/85	4080K $\pm 3\%$
Maximum dissipation at 25°C	0.12 W
Thermal dissipation factor	2 mW/°C
Thermal time constant	5 s
Termination	AgPdPt (for conductive adhesive)



MSL 1



AEC-Q200
based qualification

Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
0805	2.0 ± 0.3	1.25 ± 0.2	1.3 max	0.2 min
	(0.079 ± 0.012)	(0.049 ± 0.008)	(0.051) max	(0.008) min



How to Order (Packaging options)

NC	12	N0	0563	J	--
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NC = AgPdPt for conductive adhesive	12 = 0805	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%^*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BB = Cardboard tape (180mm reel, 4,000 pcs/reel) BF = Cardboard tape (180mm reel, 2,000 pcs/reel) BD = Cardboard tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)

* For selected PNs

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

Material Table

N0 (B25/85 = 4080K $\pm 3\%$)

T (°C)	R(T) / R25	TF (%)	α (%/°C)
-55	110.1	24.01	-7.50
-50	75.89	20.74	-7.25
-45	52.97	17.83	-7.01
-40	37.42	15.25	-6.78
-35	26.75	12.95	-6.56
-30	19.33	10.91	-6.35
-25	14.11	9.11	-6.14
-20	10.41	7.52	-5.95
-15	7.758	6.12	-5.76
-10	5.834	4.90	-5.58
-5	4.426	3.83	-5.41
0	3.387	2.91	-5.24
5	2.614	2.11	-5.08
10	2.033	1.43	-4.93
15	1.593	0.86	-4.78
20	1.258	0.39	-4.64
25	1.000	0.00	-4.51
30	0.8004	0.37	-4.37
35	0.6449	0.80	-4.25
40	0.5228	1.26	-4.13
45	0.4264	1.77	-4.01
50	0.3497	2.32	-3.90
55	0.2885	2.90	-3.79
60	0.2392	3.51	-3.68
65	0.1994	4.14	-3.58
70	0.1671	4.80	-3.49
75	0.1406	5.48	-3.39
80	0.1189	6.17	-3.30
85	0.1010	6.88	-3.22
90	0.0862	7.60	-3.13
95	0.0738	8.33	-3.05
100	0.0635	9.08	-2.97
105	0.0548	9.83	-2.90
110	0.0475	10.58	-2.83
115	0.0413	11.35	-2.76
120	0.0360	12.11	-2.69
125	0.0315	12.89	-2.62
130	0.0277	13.66	-2.56
135	0.0244	14.43	-2.50
140	0.0216	15.21	-2.44
145	0.0191	15.98	-2.38
150	0.0170	16.76	-2.33

B25/50	B25/75	B25/85	B25/100	B Tol
4049 K	4072 K	4080 K	4090 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
4,377,066	6,165,451	7,953,836
3,155,876	4,249,804	5,343,733
2,289,129	2,966,457	3,643,785
1,671,428	2,095,746	2,520,063
1,228,939	1,497,782	1,766,626
910,099	1,082,326	1,254,553
678,899	790,436	901,972
510,139	583,155	656,171
386,118	434,439	482,760
294,351	326,685	359,020
225,981	247,868	269,756
174,696	189,691	204,686
135,965	146,372	156,778
106,522	113,844	121,165
83,993	89,221	94,449
66,644	70,437	74,231
53,200	56,000	58,800
42,416	44,824	47,232
34,019	36,112	38,204
27,441	29,275	31,109
22,258	23,876	25,493
18,151	19,585	21,019
14,879	16,155	17,432
12,257	13,397	14,537
10,147	11,168	12,189
8,438.9	9,355.7	10,272
7,050.1	7,875.1	8,700.0
5,915.6	6,659.4	7,403.2
4,984.6	5,656.5	6,328.4
4,217.3	4,825.2	5,433.2
3,582.1	4,133.1	4,684.2
3,054.1	3,554.5	4,054.8
2,613.6	3,068.6	3,523.5
2,244.6	2,658.9	3,073.3
1,934.3	2,312.3	2,690.2
1,672.4	2,017.7	2,363.1
1,450.7	1,766.6	2,082.6
1,262.2	1,551.8	1,841.3
1,101.6	1,367.3	1,633.0
964.2	1,208.4	1,452.6
846.3	1,071.0	1,295.8
744.9	952.0	1,159.1