


# F98 Series ----- F981C225MMA

## Resin-Molded Chip, High CV Undertab



### PRODUCT SPECIFICATIONS :

Nominal Capacitance @ 120Hz	2.2 $\mu$ F	
Capacitance Tolerance	M = $\pm$ 20%	
Rated Voltage DC (V <sub>R</sub> )	< 85°C	16 V
Category Voltage DC (V <sub>C</sub> )	< 125°C	10 V
Surge Voltage (V <sub>S</sub> )	< 85°C	20 V
Temperature Range	-55°C to +125°C	
DC Leakage Current max. @ V <sub>R</sub>	0.5 $\mu$ A	
Dissipation Factor max. @ 120Hz	6 %	
ESR max. @ 100kHz	10 $\Omega$	
Typical weight (M case)	6 mg	
Moisture sensitivity level:	MSL 3	
Reflow specification: meets J-STD-020 standard		
100% surge current tested		
All technical data relates to an ambient temperature of +20°C, Capacitance is measured at 120Hz, 0.5RMS with DC bias of 1.5V,		
DC Leakage Current is measured at rated voltage after 5 minutes		




LEAD-FREE  
LEAD-FREE COMPATIBLE  
COMPONENT




RMS value of Ripple Current (mA) @100kHz			
25°C	60°C	85°C	125°C
50	—	45	20

### HOW TO ORDER :



Special Code	
LZT	Rated temp. 60°C
AXE	Rated temp. 60°C, H dimension 1.0mm Max

### MARKING :




RV	*	Cap	**
2.5	e	1	A
4	G	2.2	J
6.3	J	4.7	S
10	A	10	a
16	C	22	J
20	D	33	n
25	E	47	s
35	V	68	w
		100	A
		220	J

F98 Series ----- F981C225MMA  
Resin-Molded Chip, High CV Undertab



CASE DIMENSIONS: millimetres

Case Code	EIA Code	EIA Metric	L	W <sub>1</sub>	W <sub>2</sub>	H	S <sub>1</sub>	S <sub>2</sub>
M	0603	1608-09	1.6 +0.2/-0.1	0.85 +0.2/-0.1	0.65±0.1	0.8±0.1	0.5±0.1	0.6±0.1



PACKAGING INFORMATION :

Packaging Code	Reel Size	Tape Width	Quantity (pcs)
A	180 mm	8 mm	4,000

Issued by: KYOCERA AVX Technical Marketing Team  
Tantalum Division  
More details at: [www.kyocera-avx.com](http://www.kyocera-avx.com)

Version: 10/2021

**NORTH AMERICA**  
Tel: +1 864-967-2150

**CENTRAL AMERICA**  
Tel: +55 11-46881960

**EUROPE**  
Tel: +44 1276-697000

**ASIA**  
Tel: +65 6286-7555

**JAPAN**  
Tel: +81 740-321250

[WWW.KYOCERA-AVX.COM](http://WWW.KYOCERA-AVX.COM)



NOTICE: Specifications are subject to change without notice. Contact your nearest KYOCERA AVX Sales Office for the latest specifications. Specifications are typical and may not apply to all applications. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements or suggestions concerning possible use of our product are made without responsibility or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should not assume that all safety measures are indicated or that other measures are indicated or that measures may not be required. All samples are provided for testing purposes only. Provision of samples shall not constitute any offer of sale nor shall it constitute any commitment of any kind. Samples may not be incorporated in any product offered for commercial sale. Recipient assumes all risks and liability resulting from such testing. Samples are for the exclusive use of the direct recipient and shall not be sold, lent, given, or otherwise transferred to any other party. All unused samples shall be destroyed or returned to KYOCERA AVX.