

NTC SMD Thermistor with AgPdPt termination

for Automotive, Industrial and General applications

To view data online visit:

SpiCAT



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. AgPdPt termination termination for conductive adhesive assembly (not suitable for lead free soldering - use NB series).

Characteristics

Case Size	1206
Operating temperature	-55°C to +150°C
Resistance	47 kOhm
Tolerance on Resistance (25°C)	$\pm 20\%$
B 25/85	3950K $\pm 3\%$
Maximum dissipation at 25°C	0.24 W
Thermal dissipation factor	4 mW/°C
Thermal time constant	7 s
Termination	AgPdPt (for conductive adhesive)



MSL 1




AEC-Q200
based qualification

Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
1206	3.2 ± 0.4	1.6 ± 0.25	1.5 max	0.2 min
	(0.126 ± 0.016)	(0.063 ± 0.01)	(0.059) max	(0.008) min



How to Order (Packaging options)

NC

Type

NC = AgPdPt for conductive adhesive

20

Size

20 = 1206

M0

Material Code

See Datasheet

0473

Resistance (Ohm)

2 Sig. Digits + Number of Zeros

M

Tolerance

H = $\pm 3\%*$
J = $\pm 5\%$
K = $\pm 10\%$
M = $\pm 20\%$

* For selected PNs

BA

Suffix: Packaging

BA = Plastic tape (180mm reel, 3,000 pcs/reel)
BE = Plastic tape (180mm reel, 1,500 pcs/reel)
BC = Plastic tape (330mm reel, 10,000 pcs/reel)
-- = Bulk (5000 pcs/bag)

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

Material Table

M0 (B25/85 = 3950K $\pm 3\%$)

T (°C)	R(T) / R25	TF (%)	α (%/°C)
-55	99.59	15.64	-7.42
-50	68.97	14.25	-7.16
-45	48.40	12.94	-6.91
-40	34.38	11.69	-6.67
-35	24.71	10.51	-6.45
-30	17.97	9.39	-6.23
-25	13.20	8.33	-6.02
-20	9.804	7.31	-5.82
-15	7.352	6.35	-5.63
-10	5.565	5.43	-5.45
-5	4.251	4.55	-5.28
0	3.275	3.70	-5.11
5	2.544	2.90	-4.95
10	1.992	2.13	-4.80
15	1.572	1.39	-4.65
20	1.249	0.68	-4.51
25	1.000	0.00	-4.38
30	0.8057	0.66	-4.25
35	0.6534	1.30	-4.12
40	0.5331	1.92	-4.00
45	0.4376	2.53	-3.89
50	0.3612	3.12	-3.77
55	0.2998	3.70	-3.67
60	0.2501	4.26	-3.57
65	0.2097	4.81	-3.47
70	0.1767	5.35	-3.37
75	0.1496	5.87	-3.28
80	0.1272	6.38	-3.19
85	0.1087	6.88	-3.11
90	0.0932	7.37	-3.03
95	0.0803	7.84	-2.95
100	0.0694	8.31	-2.87
105	0.0602	8.76	-2.80
110	0.0524	9.21	-2.73
115	0.0458	9.64	-2.66
120	0.0402	10.07	-2.60
125	0.0353	10.48	-2.53
130	0.0312	10.89	-2.47
135	0.0276	11.29	-2.41
140	0.0245	11.68	-2.36
145	0.0218	12.06	-2.30
150	0.0194	12.43	-2.25

B25/50	B25/75	B25/85	B25/100	B Tol
3925 K	3944 K	3950 K	3958 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
3,012,627	4,680,740	6,348,853
2,131,461	3,241,798	4,352,135
1,525,368	2,274,570	3,023,771
1,103,697	1,615,829	2,127,960
807,087	1,161,527	1,515,967
596,222	844,441	1,092,661
444,774	620,579	796,383
334,927	460,791	586,655
254,494	345,536	436,579
195,059	261,565	328,071
150,755	199,796	248,836
117,448	153,937	190,426
92,205	119,590	146,974
72,923	93,645	114,366
58,084	73,888	89,691
46,580	58,725	70,869
37,600	47,000	56,400
30,046	37,869	45,692
24,168	30,708	37,249
19,563	25,056	30,548
15,932	20,565	25,198
13,050	16,975	20,900
10,750	14,089	17,428
8,902.9	11,755	14,607
7,411.5	9,857.2	12,303
6,200.7	8,306.1	10,412
5,212.6	7,031.8	8,851.0
4,402.3	5,979.9	7,557.5
3,734.5	5,107.3	6,480.2
3,181.6	4,380.3	5,579.1
2,721.7	3,771.9	4,822.1
2,337.6	3,260.6	4,183.6
2,015.4	2,829.2	3,642.9
1,744.1	2,463.6	3,183.2
1,514.7	2,152.8	2,790.9
1,320.0	1,887.5	2,455.0
1,154.2	1,660.2	2,166.3
1,012.4	1,464.9	1,917.4
890.8	1,296.4	1,702.0
786.2	1,150.7	1,515.2
695.9	1,024.2	1,352.6
617.7	914.1	1,210.6