

NTC SMD Thermistor with AgPdPt termination

for Automotive, Industrial and General applications

To view data online visit:

SpiCAT



KYOCERA AVX Chip NTC Thermistors are high quality devices developed especially for surface mounting applications. They are widely used for temperature compensation, but can also achieve temperature control of printed circuits in a wide range of applications, including automotive, industrial and general purpose. AgPdPt termination termination for conductive adhesive assembly (not suitable for lead free soldering - use NB series).

Characteristics

Case Size	1206
Operating temperature	-55°C to +150°C
Resistance	1200 Ohm
Tolerance on Resistance (25°C)	$\pm 10\%$
B 25/85	3910K $\pm 3\%$
Maximum dissipation at 25°C	0.24 W
Thermal dissipation factor	4 mW/°C
Thermal time constant	7 s
Termination	AgPdPt (for conductive adhesive)



MSL 1




AEC-Q200
based qualification

Dimensions

mm (inches)

Size (EIA)	Length (L)	Width (W)	Thickness (T)	Terminal (t)
1206	3.2 ± 0.4	1.6 ± 0.25	1.5 max	0.2 min
	(0.126 ± 0.016)	(0.063 ± 0.01)	(0.059) max	(0.008) min



How to Order (Packaging options)

NC	20	MC	0122	K	BA
Type	Size	Material Code	Resistance (Ohm)	Tolerance	Suffix: Packaging
NC = AgPdPt for conductive adhesive	20 = 1206	See Datasheet	2 Sig. Digits + Number of Zeros	H = $\pm 3\%*$ J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	BA = Plastic tape (180mm reel, 3,000 pcs/reel) BE = Plastic tape (180mm reel, 1,500 pcs/reel) BC = Plastic tape (330mm reel, 10,000 pcs/reel) -- = Bulk (5000 pcs/bag)
				* For selected PNs	

NOTICE: Specifications are subject to change without notice. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee or responsibility of any kind, expressed or implied. Specifications are typical and may not apply to all applications.

Material Table

MC (B25/85 = 3910K $\pm 3\%$)

T (°C)	R(T) / R25	TF (%)	α (%/°C)
-55	100.6	23.00	-7.56
-50	69.29	19.90	-7.27
-45	48.40	17.10	-7.00
-40	34.27	14.60	-6.75
-35	24.57	12.40	-6.50
-30	17.83	10.50	-6.27
-25	13.09	8.70	-6.05
-20	9.710	7.20	-5.84
-15	7.282	5.90	-5.64
-10	5.514	4.70	-5.45
-5	4.215	3.70	-5.27
0	3.250	2.80	-5.10
5	2.528	2.00	-4.93
10	1.982	1.40	-4.77
15	1.567	0.80	-4.62
20	1.247	0.40	-4.48
25	1.000	0.00	-4.34
30	0.8072	0.40	-4.21
35	0.6559	0.80	-4.08
40	0.5362	1.20	-3.96
45	0.4410	1.70	-3.85
50	0.3647	2.20	-3.74
55	0.3033	2.80	-3.63
60	0.2535	3.40	-3.53
65	0.2130	4.00	-3.43
70	0.1798	4.60	-3.34
75	0.1525	5.20	-3.25
80	0.1300	5.90	-3.16
85	0.1112	6.60	-3.08
90	0.0955	7.30	-2.99
95	0.0824	8.00	-2.92
100	0.0713	8.70	-2.84
105	0.0620	9.40	-2.77
110	0.0541	10.10	-2.70
115	0.0473	10.90	-2.63
120	0.0415	11.60	-2.57
125	0.0366	12.30	-2.51
130	0.0323	13.10	-2.45
135	0.0286	13.80	-2.39
140	0.0254	14.60	-2.33
145	0.0227	15.30	-2.28
150	0.0203	16.10	-2.23

B25/50	B25/75	B25/85	B25/100	B Tol
3887 K	3904 K	3910 K	3917 K	$\pm 3\%$

R Min (Ω)	R Nom (Ω)	R Max (Ω)
80,882	120,720	160,558
58,287	83,148	108,009
42,340	58,080	73,820
31,007	41,124	51,241
22,880	29,484	36,088
17,010	21,396	25,782
12,771	15,708	18,645
9,647.9	11,652	13,656
7,349.0	8,738.4	10,128
5,644.1	6,616.8	7,589.5
4,365.1	5,058.0	5,750.9
3,400.8	3,900.0	4,399.2
2,669.6	3,033.6	3,397.6
2,107.3	2,378.4	2,649.5
1,677.3	1,880.4	2,083.5
1,340.8	1,496.4	1,652.0
1,080.0	1,200.0	1,320.0
867.9	968.6	1,069.4
702.1	787.1	872.1
571.4	643.4	715.5
467.3	529.2	591.1
384.2	437.6	491.0
317.4	364.0	410.5
263.4	304.2	345.0
219.8	255.6	291.4
184.3	215.8	247.3
155.2	183.0	210.8
131.2	156.0	180.8
111.3	133.4	155.6
94.8	114.6	134.5
81.1	98.9	116.7
69.6	85.6	101.6
60.0	74.4	88.8
51.8	64.9	77.9
44.9	56.8	68.6
39.1	49.8	60.6
34.1	43.9	53.7
29.8	38.8	47.7
26.2	34.4	42.5
23.0	30.5	38.0
20.3	27.2	34.1
18.0	24.3	30.6