
# Tantalum Product - **TAJ** Series

## PRODUCT SPECIFICATIONS :




| | | |
|---|---|---|
| Nominal Capacitance @ 120Hz | 4.7 µF | |
| Capacitance Tolerance (*) | K = ±10%; M = ±20% | |
| Rated Voltage DC ($V_R$) | ≤ 85°C | 50 V |
| Category Voltage DC ($V_C$) | ≤ 125°C | 33 V |
| Surge Voltage ($V_S$) | ≤ 85°C | 65 V |
| | ≤ 125°C | 40 V |
| Temperature Range | -55°C to +125°C | |
| Direct Leakage Current max. @ $V_R$ | 2.4 µA | |
| Dissipation Factor max. @ 120Hz | 6 % | |
| ESR max. @ 100kHz | 1.4 Ohm | |
| Typical weight (D case) | 290 mg | |

RoHS COMPLIANT

LEAD-FREE

LEAD-FREE COMPATIBLE COMPONENT


*Moisture sensitivity level: meets MSL 1*
*Reflow specification: meets J-STD-020 standard*
*For AEC-Q200 availability, please contact KYOCERA AVX*
*100% surge current tested*
*All technical data relates to an ambient temperature of +25°C, Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.*
*KYOCERA AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.*


| RMS value of Ripple Current (mA) @100kHz | | | RMS value of Ripple Voltage (mV) @100kHz | | |
|---|---|---|---|---|---|
| 25˚C | 85˚C | 125˚C | 25˚C | 85˚C | 125˚C |
| 327 | 295 | 131 | 458 | 412 | 183 |

## HOW TO ORDER:

| TAJ | D | 475 | * | 050 | # | NJ |
|---|---|---|---|---|---|---|
| Type | Case code | Capacitance Value | Cap. Tolerance | Rated DC | Packaging | Suffix |

## DRAWING AND DIMENSIONS:



# Tantalum Product - **TAJ** Series

## CASE DIMENSIONS: millimetres

| Case | | | | | | | |
|---|---|---|---|---|---|---|---|
| EIA | Size | L ±0.2 | W +0.2 –0.1 | H +0.2 –0.1 | A +0.3 –0.2 | S min. | W1 ±0.2 |
| 7343-31 | D | 7.3 | 4.3 | 2.9 | 1.3 | 4.4 | 2.4 |

## PACKAGING INFORMATION:

| Reel Size (#) | R = 7” Reel<br>Pure Tin Termination | S = 13” Reel<br>Pure Tin Termination | A = 7” Reel<br>Gold Plated Termination | B = 13” Reel<br>Gold Plated Termination |
|---|---|---|---|---|
| Quantity | 500 | 2500 | 500 | 2500 |
| Tape Width | 12 mm | 12 mm | 12 mm | 12 mm |

Issued by: KYOCERA AVX Technical Marketing Team
Tantalum Division
More details at: www.kyocera-avx.com
Version: 10/2021

**NORTH AMERICA**
Tel: +1 864-967-2150

**CENTRAL AMERICA**
Tel: +55 11-46881960

**EUROPE**
Tel: +44 1276-697000

**ASIA**
Tel: +65 6286-7555

**JAPAN**
Tel: +81 740-321250

WWW.KYOCERA-AVX.COM

**NOTICE:** Specifications are subject to change without notice. Contact your nearest KYOCERA AVX Sales Office for the latest specifications. Specifications are typical and may not apply to all applications. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements or suggestions concerning possible use of our product are made without responsibility or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should not assume that all safety measures are indicated or that other measures are indicated or that measures may not be required. All samples are provided for testing purposes only. Provision of samples shall not constitute any offer of sale nor shall it constitute any commitment of any kind. Samples may not be incorporated in any product offered for commercial sale. Recipient assumes all risks and liability resulting from such testing. Samples are for the exclusive use of the direct recipient and shall not be sold, lent, given, or otherwise transferred to any other party. All unused samples shall be destroyed or returned to KYOCERA AVX.