

# Tantalum Product - TAJ AUTOMOTIVE



## PRODUCT SPECIFICATIONS :

Nominal Capacitance @ 120Hz	33 $\mu$ F
Capacitance Tolerance (*)	K = $\pm$ 10%; M = $\pm$ 20%
Rated Voltage DC (V <sub>R</sub> )	$\leq$ 85°C 35 V
Category Voltage DC (V <sub>C</sub> )	$\leq$ 125°C 23 V
Surge Voltage (V <sub>S</sub> )	$\leq$ 85°C 46 V
	$\leq$ 125°C 28 V
Temperature Range	-55°C to +125°C
Direct Leakage Current max. @ V <sub>R</sub>	11.6 $\mu$ A
Dissipation Factor max. @ 120Hz	6 %
ESR max. @ 100kHz	0.9 Ohm
Typical weight ( case)	512 mg



Moisture sensitivity level: meets MSL 3

Reflow specification: meets J-STD-020 standard

Meets requirements of AEC-Q200

100% surge current tested

All technical data relates to an ambient temperature of +25°C, Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.



KYOCERA AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

RMS value of Ripple Current (mA) @100kHz			RMS value of Ripple Voltage (mV) @100kHz		
25°C	85°C	125°C	25°C	85°C	125°C
428	385	171	385	347	154

## HOW TO ORDER:

TAJ	E	336	*	035	#	NJ	V
Type	Case code	Capacitance Value	Cap. Tolerance	Rated DC	Packaging Automotive Pure Tin T = 7" Reel U = 13" Reel	Suffix	Vacuum packing

## DRAWING AND DIMENSIONS:



# Tantalum Product - TAJ Series



## CASE DIMENSIONS: millimetres

Case							
EIA	Size	L $\pm 0.2$	W $+0.2 -0.1$	H $+0.2 -0.1$	A $+0.3 -0.2$	S min.	W1 $\pm 0.2$
7343-43	E	7.3	4.3	4.1	1.3	4.4	2.4

## PACKAGING INFORMATION:

Reel Size (#)	T = 7" Reel Automotive Pure Tin	U = 13" Reel Automotive Pure Tin
Quantity	400	1500
Tape Width	12 mm	12 mm

Issued by: KYOCERA AVX Technical Marketing Team  
Tantalum Division

More details at: [www.kyocera-avx.com](http://www.kyocera-avx.com)

Version: 10/2021

**NORTH AMERICA**  
Tel: +1 864-967-2150

**CENTRAL AMERICA**  
Tel: +55 11-46881960

**EUROPE**  
Tel: +44 1276-697000

**ASIA**  
Tel: +65 6286-7555

**JAPAN**  
Tel: +81 740-321250

[WWW.KYOCERA-AVX.COM](http://WWW.KYOCERA-AVX.COM)



**NOTICE:** Specifications are subject to change without notice. Contact your nearest KYOCERA AVX Sales Office for the latest specifications. Specifications are typical and may not apply to all applications. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements or suggestions concerning possible use of our product are made without responsibility or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should not assume that all safety measures are indicated or that other measures are indicated or that measures may not be required. All samples are provided for testing purposes only. Provision of samples shall not constitute any offer of sale nor shall it constitute any commitment of any kind. Samples may not be incorporated in any product offered for commercial sale. Recipient assumes all risks and liability resulting from such testing. Samples are for the exclusive use of the direct recipient and shall not be sold, lent, given, or otherwise transferred to any other party. All unused samples shall be destroyed or returned to KYOCERA AVX.